SATCO | NUVO



Project / Job Name:

Location:

Fixture Type:

Notes:

62-8134 - Anders; 10-Inch LED Flush Mount; 18 Watts; 3000K/4000K/5000K CCT Selectable; Smoked Graphite and Matte Black Finish

GENERAL

Company	NUVO
EA Height	8.6
EA Width	13.6
EA Length	13.6
Mounting Height	14.0
Mounting Length	8.0
Mounting Width	14.0
Bulb Included	Integrated
Diameter	12.0
Material	Aluminum / Steel
Includes	Mounting Strap/Plastic Anchors
Status	Active
Style	Modern and Contemporary
Surge Protection	Built-in surge protection - 2KV
Total Harmonic Distortion	0.45
Up Down Installation	Down
CCT Selectable	Yes
Wattage Selectable	No
Collection	Anders
Finish Family	Gray
Amps	0.160A
Lens Finish	White Swirl
Lens Material	Glass
Lensed	Yes
Power Factor	>0.9
Indoor Outdoor	Indoor
Product Technology	LED
Fluor Equiv	40W
Incandescent Equivalent	150W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	3000K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	30000
Beam Angle (degree)	120
Color Temp	Soft White to Daylight
CRI	90+
Dimming Type	Phase cut
Operating Frequency	60Hz
Operating Temp	-14F to +104F (-10C to +40C)
Lumens	1620L
Volts	120v
Watts	18W
Connection	Hardwire

PHYSICAL

Lamp Base	Integrated
Finish	Smoked Graphite
Housing Color	Smoked Graphite
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Round

ADDITIONAL INFO

Warranty	3-Years

FEATURES

Flicker Free	Yes

PACKAGING

UPC	045923417047
Case Cube	2.1496
Case Height	18.5
Case Length	14.17
Case Quantity	2
Case UPC	10045923417044
Case Weight	9.24
Case Width	14.17
EA Cube	0.9205
EA Height	8.6
EA Length	13.6
EA Quantity	1
EA Weight	9.9
EA Width	13.6
Pack Type	Kraft Box
Web Height	6.38
Web Width	12.0

COMPLIANCE

Air Tight	Yes
CA Prop 65	Lead
Dark Sky Rated	No
FCC Compliant	Yes
IC Rated	No
Location Rating	Damp
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cETLus
California Ban	Lawful for sale
Energy Star Certified	No
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026