

YGHP29C29 Fig. 6 Ground, Cu Wire/Rod/Rebar to Cu Wire Tap

By Burndy

Catalog # [YGHP29C29](#)

Cu Compression Ground Rod Connector, 1/0 str to 250 kcmil , 1/2"- 5/8" Rod, 3/8" to 1/2 " Rebar (Run) to 3/0 str to 250 kcmil (Tap)

Features

- Irreversible compression ground tap can be used as a tap connector or as a tap splice connector
- UL467 Listed
- Acceptable for direct burial in earth and concrete
- Prefilled with PENETROX™ compound and strip sealed

Application

For Direct Burial In Earth And Concrete

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Industry Standard(s)	Direct Burial
Certification - ETL	No
Standards - Industry Standards Met	• UL467 • IEEE 837
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Rebar Run Range	3 -4
Conductor - Rebar Run	• 3 • 4
Conductor - Rod Run Range	1/2 in-5/8 in
Conductor - Rod Run	• 1/2 in • 5/8 in
Conductor - Copper Str Run Range	1/0 -250 kcmil
Conductor - Copper Str Run	• 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil



Conductor - Copper Str Tap Range	3/0 AWG-250 kcmil
Conductor - Copper Str Tap	• 3/0 AWG • 4/0 AWG • 250 kcmil

Configuration

Physical Attribute - Number of Crimps Required	1
Connector Type	Tap

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in

General

Trade Name	HYTAP™
Die Index	997
Oxide Inhibitor Type	Penetrox E
Prefilled Oxide Inhibitor	Y
Plated	N
Sub Brand	HYTAP
UPC	781810220948
Type	Taps
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810220948
UPC 14 Digit GTIN	00781810220948

Logistics

Minimum Pack Quantity	1
Pallet Quantity	9800
Carton Quantity	30

Product Assets

[Catalog \[English\]](#)