

TUVA

HL1196201-AGB/CVL

The Tuva table lamp takes a minimal form and elevates it with a distinctive ceramic finish. The tall, cylindrical base is coated in a pale blue Silver Lake glaze, which darkens within the fine horizontal ribs to emphasize the discreet pattern. Topped with a generously sized off-white linen drum shade, Tuva's sculptural form brings quiet character to any tabletop or bedside.

*Due to the one-of-a-kind nature of the medium, exact colors and patterns may vary slightly from the image shown.

FINISHES

AGED BRASS w/ Ceramic Silver Lake
Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 24.5"
Width/Diameter: 14"
Canopy/Backplate: 4.75"
Product Weight: 5lb
Canopy/Backplate Shape: Cylinder
Sloped Ceiling Compatible: No
Living Finish: No
Uplight Only: No

Shade

Shade 1: Textile
Shade 1 Finish: Off White Linen
Shade 1 Top Width: 13.25"
Shade 1 Bottom L/W: 14" / 0"
Shade 1 Height: 10.5"

ELECTRICAL



Bulb 1

Bulb Included: No
Socket: E26 Medium Base
Bulb Type: A19
Max Wattage: 15
Bulb Quantity: 1
Wire Length: 96"
Cord Type: SPT-2 BLACK FABRIC
Switch Type: ON/OFF SWITCH ON SOCKET
Gem Box Required (2"x3"): No
Dark Sky: No

SHIPPING

Carton 1: 16" x 16" x 23"
Carton 1 Weight: 11lb
Shipping Method: Ground
Country of Origin: VN

