Wimbledon | E34614-DG

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Balancing work and play, the Wimbeldon collection is a fun collection of lighting fixtures that utilizes dual-layered sound dampening felt shades that enhance the acoustics of a space. The deep ridged pattern gracefully intersects elevating the simple forms. Choose from linear or half dome configurations in various colors: Dark Grey and Light Cream felts offer more neutral tones while the Olive exterior with Black felt interior presents a more colorful option. Housed within the shades are high powered LED modules that provide ample functional down lighting.



*max overall height

MEASUREMENTS

DIMENSION	: 16" L x 16" W x 8" H
MAX OAH	: 132.5" OAH
CANOPY	: 5.5" W x 2.75" H x 5.5" L
HANGING WEIGHT	: 3.9 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 500 Rated (350 Del.)
BULB	: 1 x 12W LED DC Integrated , 12W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	:
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

- Dark Gray (DG)
- Light Cream (LC)
- Olive (OLV)

MATERIAL

PET Felt

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 25000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com