

JANTZEN

B7122-TBK

Jantzen draws inspiration from classic lantern designs, reinterpreting a traditional caged form with distinct angled edges. The wavy water glass panels lend texture and movement, subtly elevating the design. Cream-colored candles add a bright note in contrast to the robust Textured Black finish of the frame. Available as a 2-light sconce and 2-light post, Jantzen modernizes heritage influences to create a timeless outdoor staple.

FINISHES

TEXTURE BLACK

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 21.5"

Width/Diameter: 15"

Canopy/Backplate: 7"

Product Weight: 11lb

Extension: 16.25"

Top to Center: 5"

Canopy/Backplate Shape: Rectangle

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Clear Optic

Shade 1 Top Width: 12.25"

Shade 1 Bottom L/W: 0" / 6"

Shade 1 Height: 16"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: B11

Max Wattage: 10

Bulb Quantity: 2

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 33" x 18" x 25"

Carton 1 Weight: 20lb

Shipping Method: Ground

Country of Origin: VN

