



|                        |               |                               |               |
|------------------------|---------------|-------------------------------|---------------|
| <b>EAN:</b>            | 4013288027887 | <b>Size:</b>                  | 285x210x55 mm |
| <b>Part number:</b>    | 05006145001   | <b>Weight:</b>                | 641 g         |
| <b>Article number:</b> | 160 i/6 Rack  | <b>Country of origin:</b>     | CZ            |
|                        |               | <b>Customs tariff number:</b> | 82054000      |

- Insulated blades for secure work at 1,000 volts
- Smooth hard zones for high speed turning, soft grip zones for high torque transfer
- Take it easy tool finder: colour coding according to profile and size
- Hexagonal anti-roll feature against rolling away
- Lasertip tips for more secure fit in the screw head

6-piece screwdriver set with individually tested, insulated screwdrivers as per IEC 60900. Individual testing in a water bath at 10,000 volts so as to ensure safe working at the permitted voltage of 1,000 volts. Kraftform Plus handle for pleasant, ergonomic working that makes blisters and calluses a thing of the past. Hard gripping zones for high working speeds whereas soft zones ensure high torque transfer. Partially Lasertip: the tip literally bites itself into the screw head and prevents any slipping. Take it easy Tool Finder: colour coding according to profile and size. The anti-roll feature prevents any bothersome rolling away at the workplace. Including a rack for storage.

**Web link**  
<https://www.wera.de/en/05006145001>

Wera - 160 i/6 Rack  
 05006145001 - 4013288027887

Wera Werkzeuge GmbH  
 Korzter Straße 21-25  
 D-42349 Wuppertal  
 Tel: +49 (0)2 02 / 40 45-0  
 E-Mail: info@wera.de

**Individually tested**



The individual testing at 10,000 volts, in accordance with IEC 60900, ensures safe working with loads up to 1,000 volts.



Our screwdrivers are tested for dielectric strength under a 10,000 volt load to make sure that their most important property, their insulation, has been exhaustively tested. Each individual Wera VDE screwdriver is subjected to this test to guarantee safe working up to 1,000 volts.

**Reduced contact pressure**



Wera Lasertip reduces the contact pressure required and enhances force transfer - meaning less screwdriving effort is required. Screwdriving becomes safer and easier.

**Lasertip**



A precisely-focused laser creates a sharp-edged surface structure. Wera Lasertip "bites" itself into the screw head and prevents any slips out of the recess. It is available for screwdrivers for slotted, Phillips and Pozidriv screws.

**Impact strength test**



Impact strength tested at -40°C, guaranteeing safety even under extreme conditions.

**Multicomponent Kraffform handle**




Wera produces the Kraffform handle out of several materials with different properties. A resistant plastic is used for the core which ensures that the blade is held securely even under high strain. A softer material is used for the coloured soft zones, which provides high frictional resistance and allows the transfer of high forces - resulting in less required screwdriving effort. The red sections with their hard surfaces prevent any "sticking" of the hand to the handle, making rapid repositioning of the hand possible.

**Rapid hand repositioning**



The hard materials used for the handle ensure rapid hand repositioning without any danger of the skin "sticking" to the handle. The surrounding hard zones with large diameters glide like wheels through the hand.

**Take it easy Tool Finder**



Screwdrivers with Take it easy tool finder: colour coding according to profile and size stamp.



**Web link**  
<https://www.wera.de/en/05006145001>

Wera - 160 i/6 Rack  
 05006145001 - 4013288027887



Wera Werkzeuge GmbH  
 Korzter Straße 21-25  
 D-42349 Wuppertal  
 Tel: +49 (0)2 02 / 40 45-0  
 E-Mail: info@wera.de

Set contents:

**162 i PH VDE Insulated screwdriver for Phillips screws, PH 1 x 80 mm**

|   |             |    |               |
|---|-------------|----|---------------|
|  | 05006152001 | 1x | PH 1 x 80 mm  |
|  | 05006154001 | 1x | PH 2 x 100 mm |

**160 i VDE Insulated screwdriver for slotted screws, 0.4 x 2.5 x 80 mm**

|   |                           |    |                    |
|---|---------------------------|----|--------------------|
|  | 05006100001 <sup>1)</sup> | 1x | 0.4 x 2.5 x 80 mm  |
|  | 05006110001 <sup>1)</sup> | 1x | 0.6 x 3.5 x 100 mm |
|   | 05006115001               | 1x | 0.8 x 4 x 100 mm   |
|   | 05006120001               | 1x | 1 x 5.5 x 125 mm   |

1) Without Lasertip

Web link

<https://www.wera.de/en/05006145001>

Wera - 160 i/6 Rack  
05006145001 - 4013288027887

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)