
PARTS BREAKDOWN

GML01



1
2
3
4
5
6
7
8
9
10
11
12
13
14
15
16
17
18
19
20
21
22
23
24
25
26
27
28
29
30
31
32
33
34
35
36
37
38
39
40
41
42
43
44
45
46
47
48
49
50
51
52
53
54
55
56
58
59
158
159
A
B

Products with multiple versions are listed in subsiding order with the newest version on top not indented.

Section	Fig. No.	Part No.	Description	GML01	Tech Bulletin	Notes
1	1	327425-6	DRIVING LEVER	1		
1	2	911138-5	P.H.SCREW M4X20 WITH WR	1		
1	3	459858-8	DRIVING LEVER SUPPORT R	1		
1	3	931102-0	HEX. NUT M4	1		
1	4	253814-8	FLAT WASHER 8	1		
1	5	265620-9	TAPPING SCREW FLANGE 4X18	1		
1	6	265620-9	TAPPING SCREW FLANGE 4X18	1		
1	7	253814-8	FLAT WASHER 8	1		
1	8	413B10-4	DRIVING LEVER SUPPORT L	1		
1	8	931102-0	HEX. NUT M4	1		
1	9	268225-4	PIN 5	1		
1	10	911138-5	P.H.SCREW M4X20 WITH WR	1		
1	11	232566-4	TORSION SPRING 12	1		
1	12	327424-8	SWITCH LEVER	1		
1	13	266424-2	TAPPING SCREW 4X20	6		
1	14	183X93-7	SWITCH BOX SET	1		Inc. 23
1	15	231227-3	COMPRESSION SPRING 15	1		
1	16	459856-2	SWITCH LEVER SUPPORT R	1		
1		931102-0	HEX. NUT M4	1		Inc with 16
1	17	459857-0	LOCK OFF BUTTON	1		
1	18	911138-5	P.H.SCREW M4X20 WITH WR	1		
1	19	632T11-3	SWITCH UNIT	1		
1	20	266424-2	TAPPING SCREW 4X20	2		
1	21	687123-7	STRAIN RELIEF	1		
1	22	141M31-9	SWITCH CIRCUIT COMPLETE	1		Inc with 22
1		539258-9	SWITCH PLATE ASS'Y	1		Inc with 22
1		266490-9	TAPPING SCREW PT 2X6	3		
1	23	183X93-7	SWITCH BOX SET	1		Inc 14
1	24	413A98-8	DRIVING LEVER HOLDER	1		
1	25	413A98-8	DRIVING LEVER HOLDER	1		
1	26	266424-2	TAPPING SCREW 4X20	5		
1	27	183U35-3	LEVER BOX SET	1		Inc 38
1	28	651083-9	SWITCH C3XA-1PSPM	1		
1	29	620J45-8	DIAL CIRCUIT	1		

Products with multiple versions are listed in subsiding order with the newest version on top not indented.

Section	Fig. No.	Part No.	Description	GML01	Tech Bulletin	Notes
1	30	266424-2	TAPPING SCREW 4X20	2		
1	31	687123-7	STRAIN RELIEF	1		
1	32	413A95-4	LEVER BOX C	1		
1	33	213A12-2	O-RING 18	1		
1	34	413B01-5	SPEED LEVER	1		
1	35	459863-5	SWITCH LEVER SUPPORT L	1		
1		931102-0	HEX. NUT M4	1		Inc with 35
1	36	232575-3	TORSION SPRING 12	1		
1	37	911138-5	P.H.SCREW M4X20 WITH WR	1		
1	38	183U35-3	LEVER BOX SET	1		Inc 27
1	39	266424-2	TAPPING SCREW 4X20	5		
1	40	699215-0	POWER SUPPLY CORD UNIT	1		
1	41	327871-3	HANDLE UPPER	1		
1	42	699216-8	POWER SUPPLY CORD UNIT	1		
1	43	265C08-1	FLAT HEAD BOLT M8X50	2		
1	44	265C06-5	THUMB NUT M8	2		
1	45	413L52-8	CLAMP	2		
1		931102-0	HEX. NUT M4	2		Inc with 45
1	46	911168-6	PAN HEAD SCREW M4X40	2		
1	47	122D38-0	HANDLE LOWER ASSEMBLY	1		Inc 48-52
1	48	258004-8	SPRING PIN 2.5-16	2		
1	49	413943-1	KNOB	2		
1	50	327A66-4	LOCK HOLDER	2		
1	51	234121-8	COMPRESSION SPRING 8	2		
1	52	327A65-6	LOCK PIN	2		
1	53	265C07-3	HEX. BOLT M8	2		
1	54	136896-4	BATTERY COVER ASS'Y	1		
1	55	231037-8	COMPRESSION SPRING 7	1		
1	56	459852-0	LOCK LEVER	1		
1	58	961018-5	STOP RING E-5	1		
1	59	327536-7	ROD 6	1		
1	101	922441-9	HEX. SOCKET HEAD BOLT M8X25	4		
1	158	911163-6	PAN HEAD SCREW M4X35	1		
1	159	413944-9	CLAMP	1		
1	159	931102-0	HEX. NUT M4	1		Inc with 159



69
73
72
71
68
103
97
160
162
163
164
165
161
166
167
168
169
171
172
70
94
104
95
100
105
92
108
84
85
86
93
90
74
99
98
101
173
174
175
176
177
178
179

Products with multiple versions are listed in subsiding order with the newest version on top not indented.

Section	Fig. No.	Part No.	Description	GML01	Tech Bulletin	Notes
2	68	266424-2	TAPPING SCREW 4X20	3		
2	69	183X12-3	TERMINAL HOUSING SET	1		Inc 71
2		263005-3	RUBBER PIN 6	4		Inc with 69
2	70	632T08-2	TERMINAL UNIT	2		
2	71	183X12-3	TERMINAL HOUSING SET	1		Inc 69
2		263005-3	RUBBER PIN 6	4		Inc with 71
2	72	266424-2	TAPPING SCREW 4X20	4		
2	73	8582C9-7	GML01 SERIAL NO. LABEL	1		
2	74	8582C3-9	GML01 NAME PLATE	1		
2	84	266424-2	TAPPING SCREW 4X20	6		
2	85	687123-7	STRAIN RELIEF	2		
2	86	687051-6	STRAIN RELIEF	3		
2	90	687124-5	STRAIN RELIEF	1		
2	92	413L30-8	INNER PLATE	1		
2	93	620J46-6	LED CIRCUIT	1		
2	94	539252-1	CONTROLLER ASS'Y	1		Inc 70, 100
2	95	141M28-8	COWLING COVER COMPLETE	1		
2	97	413L22-7	COWLING UPPER	1		
2	98	413L21-9	COWLING LOWER	1		
2	99	911233-1	PAN HEAD SCREW M5X20	4		
2	100	652031-1	PAN HEAD SCREW M3X6	4		
2	103	266424-2	TAPPING SCREW 4X20	4		
2	104	266424-2	TAPPING SCREW 4X20	4		
2	105	266424-2	TAPPING SCREW 4X20	2		
2	108	422956-1	SPONGE	1		
2	160	141M30-1	STATOR BASE COMPLETE	1		
2	161	253455-0	WAVE WASHER 19	1		
2	162	620J44-0	CONTROLLER B	1		
2	163	265C89-5	FLAT HEAD SCREW M3X10	3		
2	164	629B84-7	STATOR	1		
2	165	911148-2	PAN HEAD SCREW M4X25	6		
2	166	210059-1	BALL BEARING 6000DDW	1		
2	167	519785-2	ROTOR ASS'Y	1		Inc 166,168
2	168	211332-2	BALL BEARING 6004LLU	1		


Products with multiple versions are listed in subsiding order with the newest version on top not indented.

Section	Fig. No.	Part No.	Description	GML01	Tech Bulletin	Notes
2	169	422955-3	GROMMET	2		
2	171	312D43-7	BRACKET	1		
2	172	911233-1	PAN HEAD SCREW M5X20	4		
2	173	413L53-6	BAFFLE PLATE	1		
2	174	911126-2	PAN HEAD SCREW M4X16	4		
2	175	240205-2	FAN 170	1		
2	176	312D48-7	BLADE SUPPORT 530	1		
2	177	266424-2	TAPPING SCREW 4X20	2		
2	178	191V96-5	BLADE 530 SET	1		Standard Equipment on Z and SM versions
2	178B	191W87-2	BLADE 530 SET	1		Standard Equipment on PM version
2	179	265A69-9	HEX. BOLT M10X35 WITH WG	1		


57
66
64
63
C
61
62
67
D
65
76
75
80
78
81
C
D
107
153
154

Products with multiple versions are listed in subsiding order with the newest version on top not indented.

Section	Fig. No.	Part No.	Description	GML01	Tech Bulletin	Notes
3	57	141M23-8	REAR FLAP COMPLETE	1		
3	61	232721-8	TORSION SPRING 8	1		
3	62	327A64-8	ROD 6	1		
3	63	347A56-1	HANDLE BRACKET R	1		
3	64	265B20-5	HEX.SOCKET BUTTON HEAD BOLT M8	3		
3	65	265B20-5	HEX.SOCKET BUTTON HEAD BOLT M8	3		
3	66	961018-5	STOP RING E-5	2		
3	67	347A55-3	HANDLE BRACKET L	1		
3	75	922441-9	HEX. SOCKET HEAD BOLT M8X25	2		
3	76	413L42-1	REAR GRIP	1		
3	78	413L33-2	FRONT COVER	1		
3	80	413L45-5	HEIGHT ADJUST PLATE	1		
3	81	265B20-5	HEX.SOCKET BUTTON HEAD BOLT M8	2		
3	107	141S44-6	DECK COMPLETE	1		
3	153	162C45-5	GRASS CATCHER BRACKET	1		
3	154	162C14-6	GRASS CATCHER	1		
4	77	265620-9	TAPPING SCREW FLANGE 4X18	2		
4	79	265620-9	TAPPING SCREW FLANGE 4X18	7		


102
77
79
87
88
89
184
183
182
181
180
91
96
110
114
135
186
187
132
133
134
135
136
137
138
139
140
144
142
141
143
83
82
146
147
84
90
124
86
152
148
145
125
126
127
128
129
130
131
149
150
151

Products with multiple versions are listed in subsiding order with the newest version on top not indented.

Section	Fig. No.	Part No.	Description	GML01	Tech Bulletin	Notes
4	82	922311-2	HEX. SOCKET HEAD BOLT M6X12	2		
4	83	162B98-8	HEIGHT ADJUST LEVER COMPLETE	1		
4	84	266424-2	TAPPING SCREW 4X20	6		
4	86	687051-6	STRAIN RELIEF	3		
4	87	266424-2	TAPPING SCREW 4X20	1		
4	88	413L50-2	LEAD COVER	1		
4	89	422526-6	GROMMET	1		
4	90	687124-5	STRAIN RELIEF	1		
4	91	413L35-8	DECK UNDER COVER F	1		
4	96	266424-2	TAPPING SCREW 4X20	6		
4	102	265620-9	TAPPING SCREW FLANGE 4X18	1		
4	110	232628-8	TENSION SPRING 16	1		
4	114	347A58-7	CONNECTING ROD	1		
4	124	699213-4	POWER SUPPLY CORD UNIT	1		
4	125	265324-3	HEX. FLANGE HEAD BOLT M8X12	2		
4	126	141M25-4	TIRE 230 COMPLETE	2		
4	127	210163-6	BALL BEARING 6001DDW	2		
4	128	162C00-7	FRONT SHAFT	1		
4	129	347869-4	PLATE	2		
4	130	266424-2	TAPPING SCREW 4X20	4		
4	131	252301-4	HEX. FLANGE LOCK NUT M6-10	1		
4	132	265324-3	HEX. FLANGE HEAD BOLT M8X12	2		
4	133	210163-6	BALL BEARING 6001DDW	4		
4	134	141M26-2	TIRE 230 COMPLETE	2		
4	135	227913-2	SPUR GEAR 49	2		
4	136	265B00-1	TAPPING SCREW FLANGE 4X12	4		
4	137	911213-7	PAN HEAD SCREW M5X12	4		
4	138	413L40-5	WHEEL CAP	2		
4	139	961052-5	RETAINING RING (EXT) S-12	2		
4	140	227A00-3	SPUR GEAR 12	2		
4	141	251951-2	HEX. SOCKET HEAD BOLT M5X10	6		
4	142	210163-6	BALL BEARING 6001DDW	2		
4	143	313390-5	REAR SHAFT HOLDER	2		
4	144	162C02-3	REAR SHAFT	1		

Products with multiple versions are listed in subsiding order with the newest version on top not indented.

Section	Fig. No.	Part No.	Description	GML01	Tech Bulletin	Notes
4	145	252301-4	HEX. FLANGE LOCK NUT M6-10	1		
4	146	347865-2	CLAMP 19	2		
4	147	922223-9	H.S.H.BOLT M5X16 WITH WR	4		
4	148	122E54-8	DRIVE UNIT	1		
4	149	347A59-5	BRACKET	1		
4	150	266388-0	TAPPING SCREW 5X16	2		
4	151	922223-9	H.S.H.BOLT M5X16 WITH WR	1		
4	152	683A20-1	POLYOLEFIN TUBE	1		
4	180	265620-9	TAPPING SCREW FLANGE 4X18	1		
4	181	183X16-5	GRASS GUARD SET	1		Inc 183
4	182	413L37-4	DECK UNDER COVER R	1		
4		252329-2	SQUARE NUT M5	5		Inc with 182
4	183	183X16-5	GRASS GUARD SET	1		Inc 181
4	184	265620-9	TAPPING SCREW FLANGE 4X18	1		
4	185	346545-7	PLATE	2		
4	186	266424-2	TAPPING SCREW 4X20	2		
4	187	422758-5	PROTECTIVE SHIELD	1		
4	A01	327589-6	ROD 6	1		Not Pictured
4	A02	413L55-2	MULCHING PLUG 530	1		Not Pictured
4	A03	413L57-8	DISCHARGE CHUTE	1		Not Pictured
4	A04	782210-8	SOCKET WRENCH 17	1		Not Pictured