


PRODUCT DESCRIPTION



*Height from center of outlet to the top of the fixture

MEASUREMENTS

DIMENSION	: 5" W x 25" H x 6.5" Ext
MAX OAH	: 5" W x 5" H
HANGING WEIGHT	: 2 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 600 Rated (400 Del.)
BULB	: 2 x 5W LED DC Integrated , 10W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Vertical

FINISHES OPTION

Black (BK)

Weathered Brass (WBR)

MATERIAL

Steel, Acrylic

RATINGS

cETLus
Damp Location

ADDITIONAL

INSTALL UP/DOWN: Vertical
RATED LIFE 30000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com