

Presslok™ Splice Connectors UY, Box



Part Number:
UY-BOX

With the Presslok™ series of tools and connectors, service providers can meet the demand for enhanced customer services such as high-speed internet, video-on-demand, and video conferencing. Presslok connectors also offer full wire-range capability, increased port size to accommodate up to 2.08 mm (0.082 in) insulation sizes, and solvent resistant plastic construction. As new technologies migrate into the local loop, the importance of reliable connections in the embedded plant has increased exponentially. Each connection is a potential point of failure in high-bandwidth applications, which could require additional time and expense for a technician to repair. That is where the full line of Presslok connectors can really make a difference.

Features and Benefits

- Fast installation
- Ease of Use
- Wide Range of Common Wire Gauges
- Factory-installed sealant
- Dry versions available for Central Offices and Vaults



Presslok™ Splice Connectors UY, Box

CORNING

Specifications

General Specifications

Product Type	Copper Splice Connector
--------------	-------------------------

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Design

Composition	Gel-filled
No. of connections	Two (2)
Connector Type	Butt
Conductor	26 - 22 AWG

Ordering Information

Product Number	UY-BOX
Packaging Method	Box
Units per Delivery	100/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.