APEX

pack bundle unitize warehouse transport



APEX®

Steel strapping

Mark of quality

High quality steel strap, supply a full range of options.

100% recyclable

Signode steel strap is made from raw material, which is 100% recyclable.

Application Versatility

Multiple finishes available for varying products and application equipment

Minimizes Product Damage

Offers superior corrosion resistance to protect products from surface damage

SIGNODE

APEX®
Steel strapping



Signode APEX is a cold-rolled, low carbon steel strapping. It has been engineered to yield a higher break strength at a thinner gauge.



Features and benefits

Available in three finishes, each APEX strapping product line is specially formulated to meet the demands of a range of tensioning methods, sealing devices and packaging applications.

- **Painted and waxed**

  Painted and waxed strapping is the most widely used strapping in all applications. The waxed property improves tension transmission around load corners, while the paint improves corrosion resistance.

- **Zinc painted and waxed**

  Zinc finish strapping is waxed and has a zinc-enriched coating to provide outstanding resistance to rust. It has the same improved tension transmission characteristics as painted and waxed strapping.

- **Blued and waxed**

  Blued and waxed strapping, ideal for hot applications and used in spot-welding, produces high joint strengths with basic corrosion resistance.

APEX Technical Specifications

Painted & Waxed Color	Part Number	Strap Information						Coil Information				
		Width		Gauge		Break Strength		Coil Winding	Yield		Target Weight lbs	Per Pallet
		Inch	mm	Inch	mm	lbs	N		ft/lb	M/kg		
Brown Curved Edge	0850126	3/8	9.5	0.015	0.38	650	2,889	Mill	52.4	35.2	105	12
	2X1503			0.017	0.43	870	3,867		46.1	31.0		
Black	085003			0.020	0.51	870	3,867		39.3	26.4		
	1003625	1/2	12.7	0.015	0.38	870	3,867		39.3	26.4		
	085009			0.020	0.51	1,170	5,200		29.4	19.7		
Zinc	2X1174			0.020	0.51	1,170	5,200		29.4	19.7		
Black	085200			0.023	0.58	1,330	5,911		25.6	17.2		
	085203	5/8	15.9	0.020	0.51	1,460	6,489		23.6	15.8		
	085204			0.023	0.58	1,670	7,422		20.5	13.7		
Black /Anchor	1047020	3/4	19.0	0.020	0.51	1,750	7,778		19.6	13.1		
Black	085206	3/4	19.0	0.020	0.51	1,750	7,778		19.6	13.1		
	085207			0.023	0.58	1,990	8,844		17.1	11.5		

*****Always use American Society for Testing Materials (ASTM D-3953) minimum break strengths for package design/ safety factor purposes. For proper strap selection, contact your Signode sales representative.*

The company reserves the right to make technical alterations without prior noti ication.
© 2024 Signode Industrial Group LLC / SIG 13635 Rev 200116 / **www.Signode.com**

SIGNODE
Signode Industrial Group LLC
1-800-323-2464