SATCO | NUVO



Project / Job Name:

Location:

Fixture Type:

Notes:

65-623 - LED Canopy Fixture; 25 Watt; CCT Selectable; White Finish; 120-277 Volt

WET LOCATION · DIMMABLE · c UL us LISTED · FC · RoHS COMPLIANT · CCT SELECTABLE · 50,000 HOURS · IP 65 · IC RATED · 0-10V DIMMING

GENERAL

Company	NUVO
EA Height	5.51
EA Width	11.81
EA Length	11.81
Bulb Included	Integrated
Diameter	10.03
Material	Aluminum Alloy
Fixture Type	Canopy
Status	Active
Style	Utility
Surge Protection	Built-in surge protection - 2.5KV
Total Harmonic Distortion	15%
Wire Color	White / Black / Green / Gray / Yellow
Wire Length	11.81
Wire Quantity	5
CCT Selectable	Yes
Wattage Selectable	No
Finish Family	White
Additional Info	UV stabilized powder coated finish
Amps	0.250-0.090A
Has Camera	No
IOT Enabled	No
Lens Finish	Clear
Lens Material	Polycarbonate (PC)
Power Factor	0.9
SDS Class	LED_Fixture
Indoor Outdoor	Outdoor
Product Technology	LED
Incandescent Equivalent	80W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	3000K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	150
Color Temp	Warm to Cool White
CRI	80+
Dimming Type	0-10V Dimming
Operating Frequency	50-60Hz
Operating Temp	-22F to +122F (-30C to +50C)
Lumens	2800L-3322L
Volts	120V-277V
Watts	25W
Max Lumens	3322L
Connection	Hardwire

PHYSICAL

Lamp Base	Integrated
Finish	WHITE
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Round
Mounting Procedure	Ceiling

ADDITIONAL INFO

Warranty	5-Years

PACKAGING

UPC	045923674228
Case Cube	1.085
Case Height	12.6
Case Length	12.6
Case Quantity	2
Case UPC	10045923674225
Case Weight	12.1
Case Width	11.81
EA Cube	0.4447
EA Height	5.51
EA Length	11.81
EA Quantity	1
EA Weight	5.5
EA Width	11.81
Pack Type	Box
Web Height	3.13
Web Width	10.03

COMPLIANCE

Bug Rating	B1-U3-G1
CA Prop 65	Lead
DLC ID	PLNTBHUGY0NY
FCC Compliant	Yes
IC Rated	Yes
IP Rating	IP65
Location Rating	Wet
ROHS Compliant	Yes
Safety Listing	cULus - Listed
California Ban	Lawful for sale
UL Application	Outdoor
DLC Approved	Yes
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026