SATCO | NUVO



Project / Job Name:

Location:

Fixture Type:

Notes:

62-8033 - Zion; 12 Light LED Pendant; 44 Watt; 2700K/3000K/3500K CCT; Smoked Bronze Finish; Alabaster Stone

90+ CRI | DIMMABLE | ETL | FC | RoHS | CCT SELECTABLE | 25,000 HOURS | 3 YEAR WARRANTY | 120-277V | IP 20

GENERAL

Company	NUVO
EA Height	10.5
EA Width	32.0
EA Length	32.0
Mounting Height	1.75
Bulb Included	Integrated
Diameter	27.5
Material	Aluminum / Steel
Status	Active
Style	Contemporary
Surge Protection	Built-in surge protection - 2KV
Total Harmonic Distortion	<20%
Up Down Installation	Down
Wire Color	White
CCT Selectable	Yes
Wattage Selectable	No
Collection	Zion
Finish Family	Bronze
Additional Info	White LED Rope
Amps	1.200A
Mounting Diameter	27.5
Lens Finish	Alabaster
Lens Material	Alabaster Stone
Lensed	Yes
Power Factor	>0.9
Sloped Ceiling Compatible	Yes
Indoor Outdoor	Indoor
Product Technology	LED
Incandescent Equivalent	120W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	2700K/3000K/3500K
Dimmable	Yes-Dimmable
Hours Rated	25000
Beam Angle (degree)	120
Color Temp	Warm White to Neutral White
CRI	90+
Dimming Type	Phase cut
Operating Frequency	50/60Hz
Operating Temp	-4F to +140F (-20C to +60C)
Lumens	3520L
Volts	120V-277V
Watts	44W
Connection	Hardwire

PHYSICAL

Lamp Base	Integrated
Finish	Smoked Bronze
Housing Color	Smoked Bronze
ANSI Base	Integrated
Lamp Type	Integrated LED
MOD Lamps	4.0
Fixture Shape	Round

ADDITIONAL INFO

Warranty	3-Years
Rated For Enclosed Fixture	No

FEATURES

Flicker Free	Yes

PACKAGING

UPC	045923416651
Case Cube	6.2222
Case Height	10.5
Case Length	32.0
Case Quantity	1
Case UPC	10045923416658
Case Weight	60.8
Case Width	32.0
EA Cube	6.2222
EA Height	10.5
EA Length	32.0
EA Quantity	1
EA Weight	60.8
EA Width	32.0
Pack Type	Kraft Box
Web Height	28.5
Web Width	27.5

COMPLIANCE

Air Tight	No
CA Prop 65	Lead
Dark Sky Rated	No
FCC Compliant	Yes
IC Rated	No
IP Rating	IP20
Location Rating	Dry
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cETLus
California Ban	Lawful for sale
Energy Star Certified	No
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026