



Project / Job Name:

Location:

Fixture Type:

Notes:

62-1466R1 - Lightgate; 5 Watt LED Sconce; Matte Black Finish; Square; 3000K



GENERAL

Company	NUVO
EA Height	7.25
EA Width	7.5
EA Length	8.25
Mounting Height	4.75
Mounting Width	4.75
Bulb Included	Integrated
Extends (in)	4.75
Shade Finish	Black
Material	Aluminum / Steel
Fixture Type	Sconce
Status	Active
Style	Contemporary
Surge Protection	Built-in surge protection - 1.5KV
Top To Outlet	2.5
Up Down Installation	Universal
CCT Selectable	No
Wattage Selectable	No
Collection	Lightgate
Finish Family	Black
Amps	0.042A
Has Camera	No
IOT Enabled	No
Power Factor	>0.9
Indoor Outdoor	Outdoor
Product Technology	LED
Incandescent Equivalent	20W

ELECTRICAL

CCT (Kelvin Temp)	3000K
Dimmable	Yes-Dimmable
Hours Rated	30000
Color Temp	Soft White
CRI	90+
Dimming Type	120V only, Phase cut
Operating Temp	+14F to +95F (-10C to +35C)
Lumens	240L
Volts	120v
Watts	5W

PHYSICAL

Lamp Base	Integrated
Finish	Matte Black
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Square

ADDITIONAL INFO

Warranty	3-Years
----------	---------

PACKAGING

UPC	045923450617
Case Cube	3.7825
Case Height	15.75
Case Length	23.38
Case Quantity	12
Case UPC	10045923450614
Case Weight	21.38
Case Width	17.75
EA Cube	0.2596
EA Height	7.25
EA Length	8.25
EA Quantity	1
EA Weight	1.62
EA Width	7.5
Pack Type	Box
Web Height	4.75
Web Width	4.75

COMPLIANCE

ADA Compliant	No
CA Prop 65	Lead
FCC Compliant	Yes
Location Rating	Wet
ROHS Compliant	Yes
Safety Listing	cETLus - Listed
California Ban	Lawful for sale
Title 20	Exempt
T24/JA8 Compliant	No