

Project Name

Location

Prepared By



Notes

[www] 01-20-2023 09:30:47

General

| | |
|---------------------------|-------------------------------|
| Status | Active |
| Finish | White |
| Wattage | 25W |
| CCT (Kelvin) | 2700K/3000K/3500K/4000K/5000K |
| Color Temperature | Warm White to Natural Light |
| Width (in.) | 18.9 |
| Height (in.) | 4.13 |
| Indoor or Outdoor Fixture | Indoor |

Specifications

| | |
|-----------------------|----------------------------|
| Technology | LED |
| CRI | 90 |
| Lumen Output | 2527L-2732L |
| Rated Hours | 50000 |
| Voltage | 120V |
| Dimmable | Yes-Dimmable |
| Weight (lb.) | 2.51 |
| Fixture Shape | Round |
| Fixture Material | Steel |
| Fixture Type | Flush Mount |
| Operating Temperature | -20C (-4F) to +40C (+104F) |

Compliance

| | |
|----------------------|-------------------------------|
| Safety Listing | cETLus |
| Location Rating | Damp |
| California Status | Lawful for sale in California |
| Title 20 / 24 Status | California T24 Listed |
| California Prop 65 | Lead |
| RoHS Compliant | Yes |
| FCC Compliant | Yes |

Additional Information

| | |
|----------|---------------------------|
| Warranty | 5 Year Limited - Fixtures |
|----------|---------------------------|