Project / Job Name:

Location:

Fixture Type:

Notes:



67-138 - Emergency Light; Dual Head; 120/277 Volts; White Finish

GENERAL

Company	NUVO
EA Height	9.06
EA Width	2.56
EA Length	4.72
Bulb Included	Integrated
Material	Thermo Plastic
Fixture Type	Emergency Light
Includes	Mounting hardware and accessories
Product Notes	UL94V-0, Thermoplastic, 3.6V 900mAh Ni-Cad Battery, 90 minutes duration, 24 hour charge time, 10C-40C; Path of Egress: 6 Ft.
Status	Active
Style	Utility
Surge Protection	Built-in surge protection - 3KV
CCT Selectable	No
Wattage Selectable	No
Finish Family	White
Additional Info	Input Wattage: 0.8W; Output Wattage: 2.5W; Energy Used in Maintenance Mode: 0.8W
Amps	0.007/0.003A
Has Camera	No
IOT Enabled	No
Lens Finish	Clear
Lens Material	Polycarbonate (PC)
SDS Class	LED_Fixture
Indoor Outdoor	Indoor
Product Technology	LED
Fixture Lamp Count	2
Incandescent Equivalent	6W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	5700K
Dimmable	Non-Dimmable
CRI	70+
Operating Frequency	50/60Hz
Operating Temp	+50F to +104F (+10C to +40C)
Lumens	210L
Volts	120V/277V
Watts	0.8W
Battery Chemistry	Ni-Cad

PHYSICAL

Lamp Base	Integrated
Finish	WHITE
ANSI Base	Integrated
Lamp Type	Integrated LED
Mounting Procedure	Ceiling/Wall

ADDITIONAL INFO

Warranty	2-Years

PACKAGING

UPC	045923670282
Case Cube	0.8629
Case Height	10.83
Case Length	14.57
Case Quantity	12
Case UPC	10045923670289
Case Weight	9.42
Case Width	9.45
EA Cube	0.0634
EA Height	9.06
EA Length	4.72
EA Quantity	1
EA Weight	0.77
EA Width	2.56
Pack Type	Box
Web Height	4.38
Web Length	2.38
Web Width	8.25

COMPLIANCE

CA Prop 65	Lead
FCC Compliant	Yes
Location Rating	Damp
ROHS Compliant	Yes
Safety Listing	cULus - Certified
California Ban	Lawful for sale
DLC Approved	No
Title 20	Yes
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026