

OSPREY

B5623-PBR/GRA

The Osprey hanging sconce features a sleek capsule with subtle nautical influence. Finished in Graphite with a Patina Brass hook, its streamlined capsule is completed with an opal glossy glass lens that emits a soft, diffused glow. Available in two sizes, Osprey is suitable for both indoor and outdoor use.

FINISHES

PATINA BRASS w/ GRAPHITE

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 22.75"

Width/Diameter: 5"

Canopy/Backplate: 5"

Product Weight: 5lb

Extension: 3.5"

Top to Center: 5.5"

Canopy/Backplate Shape: Rectangle

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Opal Glossy

Shade 1 Top Width: 2.5"

Shade 1 Bottom L/W: 0" / 3"

Shade 1 Height: 4.75"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: GU10

Bulb Type: MR16

Max Wattage: 10

Bulb Quantity: 1

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 26" x 7" x 8"

Carton 1 Weight: 6lb

Shipping Method: Ground

Country of Origin: VN

