



## 022-5302

### Northstar Edge 50' Cable SRL

#### FEATURES :

- Exclusive cable retraction limiter
- Simplified cable replacement system
- Semi-sealed mainspring
- Semi-sealed pawl assembly
- Oscillating, double-locking/anti-ratcheting pawls
- 360/180° swivel attachment point w/ steel carabiner
- Lifeline handle w/ mini absorber and steel swivel snap hook
- RFID equipped for easy asset tracking
- All components are Z359.12 compliant

\*\*\*Eligible for service and repair\*\*\*

Class

# 2

Anchor above or below dorsal D-ring



USER WEIGHT CAPACITY	
ANSI	130-310 lbs. (59-141 kg)
OSHA	Up to 420 lbs. (191 kg)

STANDARD COMPLIANT WITH	
ANSI	Z359.14-2021
OSHA	1910.140, 1910.66

ANSI CLASS 1	
Max. arrest force	≤ 1,800 lbs. (817 kg)
Avg. arrest force	≤ 1,350 lbs. (612 kg)
Max. arrest distance	≤ 42 in. (107 cm)
Actual arrest distance	≤ 42 in. (107 cm)
Max. free fall distance	24 in. (61 cm)
Min. required fall clearance	7ft. (2.1 m)
For full clearance requirements, see user instructions	

ANSI CLASS 2	
Max. arrest force	≤ 1,800 lbs. (817 kg)
Avg. arrest force	≤ 1,350 lbs. (612 kg)
Max. arrest distance	N/A
Actual arrest distance	76 in. (193 cm)
Max. free fall distance	72 in. (183 cm)
Min. required fall clearance	14 ft. 10 in. (4.5 m)
For full clearance requirements, see user instructions	

MATERIAL SPECIFICATION	
Cable	3/16" galvanized steel
Carabiner	YCM Plated Steel
Housing	Polycarbonate
Swivel Snap Hook	YCM Plated Steel
Shock pack	Polyester

