

SPADE

F4050-PBR

The Spade family offers a modern take on the Italian Stilnovo style. A classic tapered cone profile is softened to a pointed dome to create a modern, functional shade. Captured by a pivot, it can be directed to allow customized spot lighting wherever needed. The refined Patina Brass metalwork adds an antique note to the fixtures. Spade is available as a 1-light sconce or 5-light chandelier.

FINISHES

PATINA BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 15"

Width/Diameter: 49.25"

Minimum Height: 21.75"

Maximum Height: 64.75"

Canopy/Backplate: 6"

Hanging Type: 1-6" / 2-12" / 1-18" Stems

Product Weight: 11.9lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Steel

Shade 1 Finish: Patina Brass

Shade 1 Top Width: 4.75"

Shade 1 Height: 8"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: R30 LED

Max Wattage: 25

Bulb Quantity: 5

Bulb Included: No

Wire Length: 144"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 52" x 19" x 14"

Carton 1 Weight: 20lb

Shipping Method: Ground

Country of Origin: VN

