Pirouette - Bath Vanity | E24152-BK


Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____







PRODUCT DESCRIPTION



MEASUREMENTS

DIMENSION	: 24" L 4.75" H x 3.75" Ext
BACK PLATE	: 4" HCO
CANOPY	: 8" W x 1.5" H x 4.75" L
HANGING WEIGHT	: 2.1 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 1,350 Rated (350 Del.)
BULB	: 1 x 15W LED DC Integrated , 15W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	:
CRI	: 90 CRI
COLOR_TEMP	: 27-30-35-40-50K
LIGHTING_DIRECTION	: Indirect

FINISHES OPTION

Black (BK)

MATERIAL

Aluminum, Steel, PVC

RATINGS

cETLus
Damp Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Vertical
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com