



CT663BKSSTB



32.63" x 23.63" x 23" (H x W x D)

24" wide residential ENERGY STAR certified 5 cu.ft. refrigerator-freezer made in Europe with a stainless steel door and black cabinet

Highlights:

ENERGY STAR certified for guaranteed savings and a greener performance

Over 5 cu.ft. of storage capacity in a perfectly sized 24" footprint

Stainless steel wrapped door with professional towel bar handle adds luxury to any setting

Product Features:

24" Wide Refrigerator-Freezer	Includes a full refrigerator and freezer section for undercounter use
Peak24 Series	European-made collection for recessed installation featuring large capacity interiors, ENERGY STAR certified performances, and versatile style
ENERGY STAR certified	Rated by the DOE to perform with more efficiency than federal standards require, saving your unit energy and you on higher utility costs
Slim counterheight dimensions	Ideal 24" footprint offers full 5.1 cu.ft. storage capacity in a slim fit
Stainless steel wrapped door	Durable design with lasting elegance
Professional towel bar handle	Curved handle in brushed stainless steel offers a sturdy grip with professional elegance
Cycle defrost	This system utilizes user-friendly automatic defrost operation in the fresh food section and efficient manual defrost operation in the freezer compartment
Dual evaporator	Our unique and efficient design separately cools the refrigerator while maintaining a lower temperature in the freezer compartment by utilizing two evaporators
Adjustable glass shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up



CT663BKSSTB Specifications:

Overview	
Nominal Height	33.0" (84 cm)
Height of Cabinet	32.63" (83 cm)
Nominal Width	24.0" (61 cm)
Width	23.63" (60 cm)
Nominal Depth	23.0" (58 cm)
Depth	23.0" (58 cm)
Depth with Handle	25.25" (64 cm)
Depth with door at 90°	45.38" (115 cm)
Capacity	5.04 cu.ft. (143 L)
Defrost Type	Cycle
Door	Stainless Steel
Cabinet	Black
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Energy Usage/Year	330.0kWh/year
Amps	1.2
Voltage/Frequency	115 V AC/60 Hz
Weight	100.0 lbs. (45 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
UPC	761101068701
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Factory Reversible
Adjustable Shelves	Yes
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Wine Bottle Shelving	Yes
Interior Light	Yes
Refrigerator - Interior Height	18.0" (46 cm)
Refrigerator - Interior Width	21.0" (53 cm)
Refrigerator - Interior Depth	18.0" (46 cm)
Refrigerator - Capacity	4.5 cu.ft
Refrigerator - Shelf Type	Glass

Refrigerator - Shelf Qty	2
Refrigerator - Full Door Shelves	3
Freezer - Interior Height	5.25" (13 cm)
Freezer - Interior Width	19.0" (48 cm)
Freezer - Interior Depth	11.5" (29 cm)
Freezer - Capacity	0.6 cu.ft
Thermostat Type	Dial
Refrigerant Type	R600a
Refrigerant Amount	0.92 oz.
Level Legs	2
Compressor Step Height	5.5" (14 cm)
Compressor Step Width	21.0" (53 cm)
Compressor Step Depth	6.0" (15 cm)

