



msi

MONITOR

Optix MPG341CQRV



SPECIFICATION

Panel Size	34"
Panel Resolution	3440 x 1440
Refresh Rate	120Hz
Response time	1ms
Panel Type	VA
Brightness (nits)	400 nits
Viewing Angle	178° / 178°
Aspect Ratio	21:9
Curvature	1800R
Contrast Ratio	3000:1
DCR	100000000:1
Active Display Area (mm)	797.22(H) x 333.72(V)
Pixel Pitch (H x V)	0.23175(H)X0.23175(V)
Surface Treatment	Anti-glare
Display Colors	1.07 B
DCI-P3 / sRGB	84% / 105%
Video ports	1x DP(1.4) 2x HDMI (2.0) 1x USB Type C (DisplayPort Alternate)
USB ports	3x USB 3.2 Gen1 Type A 1x USB 3.2 Gen1 Type B (PC to Monitor)
Audio ports	1x Earphone out 1x Mic in 1x Combo Jack (PC to Monitor)
Kensington Lock	Yes
VESA Mounting	100 x 100mm
Control	5-way OSD navigation joystick
Power Type	Internal Adaptor
Power Input	100~240V, 50~60Hz
Power consumption	90W
Signal Frequency	70.56 to 214.56KHz(H) 48 to 120Hz(V)
Adjustment (Tilt)	-5° ~ 15°
Adjustment (Swivel)	-30° ~ 30°
Adjustment (Height)	0-100mm
Dimension (W x H x D)	810.6 x 324.2 x 563mm / 31.9" x 12.76" x 22.17"
Weight (NW / GW)	9.6kg / 13.51kg 21.16lbs / 29.76lbs
Frameless Design	Yes
Note	Display Port: 3440 x 1440 (Up to 120Hz) HDMI: 3440 x 1440 (Up to 100Hz) Type C: 3440 x 1440 (Up to 120Hz)

FEATURE

GameSense



Conductively enables external game alerts via RGB LED lighting with the hottest competitive online games.



120Hz Refresh Rate

Experience smooth gaming with a blazing fast 120Hz refresh rate, which gives you the upperhand in fast moving games.



VESA Certified DisplayHDR 400

Provide eye-catching detail through contrast and shadows adjustment.



1ms Fast Response Time

Eliminate screen tearing and choppy frame rates with 1ms response time.



Curved Gaming

MSI Curved Gaming Monitor will give you the most immersive and competitive edge you need to take down your opponents.



Gaming OSD APP

Customize and set the ultimate monitor modes with keyboard & mouse in a very easy way.

CONNECTIONS



- 1. Power jack
- 2. 2x HDMI 2.0a
- 3. 1x Display Port 1.2a
- 4. 1x USB Type C (DisplayPort Alternate)
- 5. 1x USB 3.2 Gen1 Type B (PC to Monitor)
- 6. 1x USB 3.2 Gen1 Type A
- 7. Combo Jack (PC to Monitor)
- 8. 2x USB 3.2 Gen1 Type A
- 9. 1x Mic in
- 10. 1x Headphone out
- 11. 1x Navi Key
- 12. 1x Kensington Lock