



P65

Technical Data



Color	Clear
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	25.98 x 15.75 x 16.73
Case Weight (lbs)	28.66
Country of Origin	Malaysia
Ventilation	Indirect
Headband	Elastic
Lens Color	Clear
Frame Material	Vinyl
Lens	Clear
Lens Coating	Anti-Scratch, Anti-Fog

Bouton® Optical 551 Softsides™

Indirect Vent Goggle with Clear Blue Body, Clear Lens and Anti-Scratch / Anti-Fog Coating

- Offers indirect ventilation through plastic hooded vents in the frame
- Soft vinyl body molds snugly to the face without pressure or irritation
- Fits comfortably over most prescription glasses
- Extended face flanges close the gaps over the nose and cheekbone areas, providing excellent protection
- Clear blue transparent frame to prevent yellowing
- Elastic headband
- Meets ANSI Z87.1
- ⚠ **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Protection from Liquid Splash, Dust and Light Impacts

SKU Information

SKU	FRAME COLOR	LENS	LENS COLOR	LENS	UPC	UPC (INNER)	UPC (CASE)
				COATING			
248-5190-300B	Clear	Clear	Clear	U	616314106514	01616314106513	02616314106512
248-5190-400B	Clear	Clear	Clear	AS/AF	616314106477	01616314106476	02616314106475
248-5190-400B-RHB					616314233852		02616314233850

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated