



Technical Data

Color	Black, Green
Sizes Available	S/M-2XL/3XL
Packaging	Bagged Each
Case Weight (lbs)	0.00
Country of Origin	Mexico
Certifications	TAA Compliant
Harness Points of Adjustment	5
Harness Style	H
Extended D-Ring	No
Coated	No
Harness Integrated Padding	Yes
Harness Integrated Chair	No
Harness Reflective Webbing	No
Webbing Material	Kevlar®/Nomex®

Miller® Revolution

Welder's Premium Full-Body Harness with Kevlar®/Nomex® DualTech™ Webbing, 5 Points of Adjustment, Back D-Ring and Quick-Connect Chest & Leg Buckles

- Designed for welders and engineered with permanent fire retardant (FR) properties
- DualTech webbing offers the durability of FR Kevlar® on the outer side, with softer FR Nomex® on the inside
- PivotLink connection points use a rotary design for mobility and as attachment points for tools and accessories
- Quick-connect buckles with dual-tab release prevent accidental opening and ensure easy donning
- ErgoArmor back shield reduces impact from snap hooks and lifelines
- Cam buckles offer one-hand adjustment for simultaneous strap adjustments
- Integrated accessory system with modular design for attaching tools and belts
- Web finials with clip-on design organizes webbing securely
- Supports a weight capacity of 400 lbs, exceeding ANSI requirements
- Meets OSHA, Certified ANSI and CSA standards for fall protection equipment

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
RKN-QC/S/MBK	Black	S/M	612230129507		
RKN-QC/UBK	Black	L/XL	612230129514		00612230302948
RKN-QC/XXL/XXXLBK	Black	2XL/3XL	612230129521		
RKN-QC/UGN	Green	L/XL	612230161064		