# **Citadel** | E30319-BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








**PRODUCT DESCRIPTION**

Vertical aluminum strands surround an acrylic LED tube that shines omnidirectional light filtered by the frame. The thin profile of the overall column extends less than 4" offering ADA compliant applications. Available in a variety of sconce sizes, the design is finished in a matte Black finish that complements most settings.




**MEASUREMENTS**

| | |
|---|---|
| DIMENSION | : 3.25" L x 3.25" W x 35.5" H |
| MAX OAH | : 4.75" W x 4.75" H |
| HANGING WEIGHT | : 5.94 lb |

**LAMPING**

| | |
|---|---|
| INPUT VOLTAGE | : 12-24V |
| LUMENS | : 840 Rated (540 Del.) |
| BULB | : 1 x 12W LED DC Integrated , 12W Total |
| BULB INCLUDED | : (Integrated) |
| DIMMABLE | : 3-in-1: Triac, ELV, or 0-10V |
| CRI | : 90 CRI |
| COLOR_TEMP | : 3000K |

**FINISHES OPTION**

Black (BK)

**MATERIAL**

Stainless Steel, Aluminum

**RATINGS**

cETLus
Wet Location

**ADDITIONAL**

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com