



Technical Data

Color	Blue/Black, Blue
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	23.46 x 13.94 x 16.34
Case Weight (lbs)	16.09
Country of Origin	Taiwan
Lens	Tinted
Frame Style	Rimless
Lens Color	Light Blue
Frame Fit	Universal
Lens Coating	FogLess 3Sixty
Bridge	Rubber
Temple	Bayonet
Base Curve	9
Construction	Metal Detectable
Certifications	CSA Z94.3 Certified, TAA Compliant

Bouton® Optical Captain™

Metal Detectable Rimless Safety Glasses with
Light Blue Lens and Anti-Scratch / Fogless®
3Sixty™ Coating

- Lightweight, rimless design provides all day user comfort
- Full metal detectable design to mitigate product loss risk
- Thin, flexible non-slip temples provide a secure fit without uncomfortable pressure points
- FogLess® 3Sixty™ enhanced hydrophobic action resists lens fogging and provides clear vision in extreme working conditions
- Silicone nose pad provides a comfortable fit
- 9 Base curve lens
- Meets ANSI Z87+
- Meets CSA Z94.3

SKU Information

SKU	FRAME COLOR	LENS	LENS COLOR	LENS COATING	UPC	UPC (INNER)	UPC (CASE)
250-46-0010	Clear	Clear	Clear	AS/AR	616314129179	01616314129178	02616314129177
250-46-0020	Clear	Clear	Clear	AS/AF	616314129155	01616314129154	02616314129153
250-46-0021	Gray	Tinted	Gray	AS/AF	616314129162	01616314129161	02616314129160
250-46-0226	Brown	Indoor Outdoor Blue	Clear	AS/AF	616314129186	01616314129185	02616314129184
250-46-0520	Clear	Clear	Clear	AS/FL360	616314200076	01616314200075	02616314200074
250-46-0521	Gray	Tinted	Gray	AS/FL360	616314209512	01616314209511	02616314209510
250-46-D515	Blue/Black				198987162832	10198987162839	20198987162836
250-46-D520	Blue	Clear	Clear	FL360/AS	616314854064	10616314854061	20616314854068
250-46-D553	Blue	Tinted	Light Blue	FL360	616314854101	10616314854108	20616314854105

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated