SIEMENS

Data sheet US2:PNW0816L1200TC

SIEMENS LOW VOLTAGE PLUG-ON NEUTRAL READY PRO SERIES ASSEMBLED LOAD CENTER. MAIN LUG WITH 8 1-INCH SPACES ALLOWING MAX 16 CIRCUITS. 1-PHASE 3-WIRE SYSTEM RATED 120/240V (200A) 100KAIC. SPECIAL FEATURES: COPPER BUS, FEED THRU LUGS, GREY TRIM NEMA TYPE 3R ENCLOSURE FOR OUTDOOR USE.

General technical data	
configuration of the busbars	COPPER BUS
number of circuits in a trunking unit	16
phase number	1
suitability for operation	RESIDENTIAL AND LIGHT COMMERCIAL ELECTRIC DISTRIBUTION
Electricity	
ampacity	200 A
voltage between phase and Ground (GND) rated value	120 V
voltage between phase and phase rated value	240 V
Model	
product brand name	SIEMENS
product sub brand name	LOAD CENTERS
product type designation	PLUG-ON NEUTRAL READY PRO SERIES
special product feature	GREY TRIM/ FEED THRU LUGS
Mechanical Design	
number of modular width units for installation width	8
General product approval	
certificate of suitability	UL

last modified: 7/9/2021

Subject to change without notice
© Copyright Siemens