

DoubleSight Wide Screen LCD Displays!



DOUBLESIGHT WIDESCREEN LCD MONITORS

- **27" & 30" Models**
- **Resolution up to 2560 x 1600**
- **IPS Panels for Greater Viewing and Superior Color Reproduction**
- **3 Viewing Options - Full Screen, Split Screen, Picture in Picture**
- **HDCP Compatible**



www.doublesight.com

DoubleSight Displays LCD Monitors widen your view!



FULL SCREEN



SPLIT SCREEN



Picture in Picture

| Features and Specs | | DS-279W | DS-309W |
|--------------------|---------------------------|--|--|
| LCD | Panel Type | S-IPS | S-IPS |
| | Back Light | LED | CCFL |
| | Visible Screen Area | 27" | 30" |
| | Pixel Pitch | 0.2331mm x 0.2331mm | 0.2331mm x 0.2331mm |
| | Max. Visible Angle | 178° / 178° | 178° / 178° |
| | Displayed Color | 1.07 Billion Colors (10 bit) | 1.07 Billion Colors (10 bit) |
| | Response Time | 6 msec (GTG) | 6 msec (GTG) |
| | Brightness | 380cd/m ² | 370cd/m ² |
| | Aspect Ratio | 16:9 | 16:10 |
| | Contrast Ratio | 1000:1 | 1000:1 |
| | Recommended Resolution | 2560 x 1440 | 2560 x 1600 |
| Interface | Interface | Digital, Analog | Digital, Analog |
| | Interface Type | DP, Dual Link DVI-D, VGA, HDMI | DP, Dual Link DVI-D, VGA, HDMI |
| Power | AC (Adapter) | 100~240V, 50~60Hz DC | 100~240V, 50~60Hz DC |
| | Power Consumption | 120W max, 1.2W Power Save Mode | 120W max, 1.2W Power Save Mode |
| Characteristics | Operating Temperature | 0~40°C | 0~40°C |
| | Storage Temperature | -20°C ~ 60°C | -20°C ~ 60°C |
| | Operating Humidity | 10 ~ 50% RH | 10 ~ 50% RH |
| | Controls | Graphic OSD, Auto Adjustment | Graphic OSD, Auto Adjustment |
| | Color | Black | Black |
| | Speakers | 2W per Channel | 2W per Channel |
| | Dimensions - Overall | 18"H x 26"W x 7.5"D | 21"H x 27"W x 7"D |
| | Dimensions - Monitor Only | 16"H x 26"W x 7.5"D | 18.5"H x 27"W x 3.5"D |
| | Dimensions - Base | 12"W x 7.5"D x 2"H | 13.5"W x 7"D x 2.5"H |
| | VESA Compatible | 100mm x 100mm | 100mm x 100mm |
| | Weight | 17 lbs Monitor and Stand; 15 lbs (monitor only) | 21 lbs Monitor and Stand; 17 lbs (monitor only) |
| | Certifications | FCC | FCC |
| | Warranty | 3 year limited warranty, parts and labor | 3 year limited warranty, parts and labor |
| Package Contents | | 27" LCD Monitor & Stand, DVI-D Cable, VGA Cable, AC Adaptor & Power Cord, Audio Cable, Users Manual CD | 30" LCD Monitor & Stand, DVI-D Cable, VGA Cable, AC Adaptor & Power Cord, Audio Cable, Users Manual CD |