

Product data sheet

Characteristics

HOM2100CP

Mini circuit breaker, Homeline, 100A, 2 pole, 120/240VAC, 10kA AIR, standard type, plug in, UL



Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	100 A
Certifications	UL Listed
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number of Poles	2P
Short Circuit Current Rating	10 kA
Number of Spaces	2
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs
Wire Size	AWG 4...AWG 2/0 aluminium/copper)1
Type of Packing	Consumer packaging

Complementary

Tightening torque	42.48 lbf.in (4.8 N.m) (AWG 4...2/0 kcmil)
Height	3.13 in (79.50 mm)
Width	2 in (50.80 mm)
Depth	2.98 in (75.69 mm)

Environment

Ambient Air Temperature for Operation	104 °F (40 °C)
---------------------------------------	----------------

Ordering and shipping details

Category	01347-HOM 2 POLE BULK 70-200AMP
Discount Schedule	CPH
GTIN	047569062858
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.40 in (8.636 cm)
Package 1 Width	2.30 in (5.842 cm)
Package 1 Length	3.80 in (9.652 cm)
Package 1 Weight	13.62 oz (386.0 g)
Unit Type of Package 2	PAL
Number of Units in Package 2	1728
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)

Package 2 Weight	1486.08 lb(US) (674.074 kg)
Unit Type of Package 3	CAR
Number of Units in Package 3	36
Package 3 Height	3.90 in (9.906 cm)
Package 3 Width	14.00 in (35.56 cm)
Package 3 Length	20.80 in (52.832 cm)
Package 3 Weight	31.20 lb(US) (14.152 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	Lifetime
----------	----------