



P65

Technical Data



Color	Black
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	27.17 x 9.45 x 12.60
Case Weight (lbs)	13.23
Country of Origin	Malaysia
Lens	Tinted
Frame Style	Semi-Rimless
Lens Color	Light Blue
Frame Fit	Round Face
Lens Coating	Anti-Scratch
Bridge	Rubber
Temple	Rubber Tips
Base Curve	8
Certifications	ANSI Z87.1

Bouton® Optical Adversary™ Semi-Rimless Safety Glasses with Black Frame, Light Blue Lens and Anti-Scratch Coating

- Lightweight, semi-rimless design provides all day user comfort
- Wraparound lens design with distortion-free viewing
- Bayonet temples with rubber tips provide a comfortable fit
- Temple tips curve out at ends for ease of placement on face
- Ribbed rubber nose pads offer a more secure fit
- Supplied with an adjustable neck cord
- 8 Base curve lens
- Meets ANSI Z87.1+
- ⚠ **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Outdoor Work
- Construction Applications
- Public Works

SKU Information

SKU	FRAME COLOR	LENS	LENS		UPC	UPC (INNER)	UPC (CASE)
			LENS COLOR	COATING			
250-28-0000	Black	Clear	Clear	AS	616314065835	01616314065834	02616314065833
250-28-0001	Black	Tinted	Gray	AS	616314065828	01616314065827	02616314065826
250-28-0002	Black	I/O	Clear	AS	616314068942	01616314068941	02616314068940
250-28-0003	Black	Tinted	Light Blue	AS	616314065842	01616314065841	02616314065840
250-28-0006	Black	Mirror	Silver	AS	616314068928	01616314068927	02616314068926
250-28-0009	Black	Tinted	Amber	AS	616314068935	01616314068934	02616314068933
250-28-0020	Black	Clear	Clear	AS/AF	616314065811	01616314065810	02616314065819
250-28-0021	Black	Tinted	Gray	AS/AF	616314068959	01616314068958	02616314068957

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated