

# PHILIPS

## Home Access

### Smart deadbolt

#### 4000 series

# Philips Built-in Wi-Fi Touchscreen Smart Deadbolt

DDL0M1040X-15HW

**Built-in smart security  
with 3 ways to unlock**



Nickel

Matte black



## Specifications

| Overview                        |                            | Modes                            |                                 | Key Features               |                              |
|---------------------------------|----------------------------|----------------------------------|---------------------------------|----------------------------|------------------------------|
| Material                        | Aluminum alloy             | Operation mode                   | Auto mode                       | Safety                     | Meets ANSI/BHMA standard     |
| Color                           | Nickel / Matte black       | Security mode                    | Away mode                       |                            | AES128                       |
| Bolt type                       | Dead bolt                  | <b>Power</b>                     |                                 |                            | Local storage                |
| Keyway                          | SC1                        | Power supply                     | 8 AA Batteries                  | Alarm                      | Low battery alarm            |
| Connectivity                    | Built-in Wi-Fi / Bluetooth | Emergency powering               | Not supported                   |                            | Wrong entry limit alarm      |
| <b>Unlock Methods</b>           |                            | <b>Operating Environment</b>     |                                 |                            | Jam alarm                    |
| Unlocking from outside          | Home Access app            | Temperature                      | From -35°C to 66°C              | Remote control             | App unlock                   |
|                                 | PIN code                   | Humidity                         | 0-95%                           |                            | Manage user accounts         |
|                                 | Key                        | <b>Installation Requirements</b> |                                 |                            | Create schedule PIN codes    |
| Unlocking from inside           | Thumb turn                 | Door thickness                   | 1-3/8 to 2 inch (35-50mm)       |                            | Simple sharing               |
|                                 | Home Access app            | Opening direction                | Left inside / Left outside      | Language                   | English / French / Spanish   |
|                                 | Voice assistant            |                                  | Right inside / Right outside    | Voice navigation           | Real person voice navigation |
| <b>Max Credentials Capacity</b> |                            | Cross bore hole                  | 1-1/2 or 2-1/8 inch (38/54mm)   | Works with voice assistant | Amazon Alexa                 |
| Master PIN code                 | 1                          | Backset                          | 2-3/8 or 2-3/4 inch (60mm/70mm) |                            | Google Assistant             |
| User PIN code                   | 100                        |                                  |                                 |                            |                              |
| One-time PIN code               | Unlimited                  |                                  |                                 |                            |                              |
| Traditional key                 | 2                          |                                  |                                 |                            |                              |



Built-in  
Wi-Fi



Built-in  
Bluetooth



Control  
through app



PIN code  
unlock



Traditional  
key