SATCO | NUVO



Project / Job Name:

Location:

Fixture Type:

Notes:

62-8129 - Amalfi; 5-Inch LED Flushmount; 12 Watt; 3000K/4000K/5000K CCT Selectable; Gilded Bronze; Alabaster Stone Lens

DAMP LOCATION | 90+ CRI | DIMMABLE | ETL US | FC | RoHS COMPLIANT | CCT SELECTABLE | 30,000 HOURS | AIR TIGHT | 3 YEAR WARRANTY | 120 VOLT

GENERAL

Company	NUVO
EA Height	12.5
EA Width	6.7
EA Length	6.7
Mounting Height	0.75
Mounting Length	14.0
Mounting Width	14.0
Bulb Included	Integrated
Diameter	5.0
Material	Aluminum / Steel
Includes	Mounting Strap/Plastic Anchors
Status	Active
Style	Transitional
Surge Protection	Built-in surge protection - 2KV
Total Harmonic Distortion	45%
Top To Outlet	8.0
Up Down Installation	Down
CCT Selectable	Yes
Wattage Selectable	No
Collection	Amalfi
Finish Family	Bronze
Amps	0.110A
Lens Finish	Alabaster
Lens Material	Alabaster Stone
Lensed	Yes
Nominal Length	5.0
Power Factor	>0.9
Indoor Outdoor	Indoor
Product Technology	LED
Fluor Equiv	32W
Incandescent Equivalent	100W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	3000K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	30000
Beam Angle (degree)	120
Color Temp	Soft White to Daylight
CRI	90+
Dimming Type	Phase cut
Operating Frequency	60Hz
Operating Temp	-14F to +104F (-10C to +40C)
Lumens	1080L
Volts	120v
Watts	12W
Connection	Hardwire

PHYSICAL

Lamp Base	Integrated
Finish	Gilded Bronze
Housing Color	Gilded Bronze
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Round

ADDITIONAL INFO

Warranty	3-Years

FEATURES

Flicker Free	Yes

PACKAGING

UPC	045923416996
Case Cube	2.4211
Case Height	13.39
Case Length	22.05
Case Quantity	6
Case UPC	10045923416993
Case Weight	23.1
Case Width	14.17
EA Cube	0.3247
EA Height	12.5
EA Length	6.7
EA Quantity	1
EA Weight	3.52
EA Width	6.7
Pack Type	Kraft Box
Web Height	10.25
Web Width	5.0

COMPLIANCE

ADA Compliant	No
Air Tight	Yes
CA Prop 65	Lead
Dark Sky Rated	No
FCC Compliant	Yes
IC Rated	No
Location Rating	Damp
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cETLus
California Ban	Lawful for sale
Energy Star Certified	No
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026