



Post Office Box 97
Benton Harbor, Michigan
Ph: 269/926-6171
Fax: 269/925-8288

PART NUMBER:
STD395

REV.

A

Model Number	Motor Voltage	RPM		HP	kW	Net Wt.	
		60 cycle	50 cycle			lbs.	kg
1023-101Q-G279	208-220/440-3 208-220/440-3	1725 ----	----- 1425	3/4	0.56	52	23,6

SOUND LEVEL LESS THAN 70 dba
NORMAL AMBIENT 1°C. - 40°C.
RELATIVE HUMIDITY 8% - 100% NON CONDENSING
ENVIRONMENT CLEAN DUST FREE

- * TECHNICAL DATA SUBJECT TO CHANGE WITHOUT NOTICE.
- * SOLID LINE IS FOR 60 Hz PERFORMANCE
DASHED LINE IS FOR 50 Hz PERFORMANCE.
- * DIMENSIONS ARE FOR REFERENCE ONLY UNLESS OTHERWISE TOLERANCED.
- * THIS PUMP MUST BE WIRED AND ENCLOSED IN CONFORMANCE WITH APPLICABLE LOCAL, STATE, NATIONAL OR INTERNATIONAL REGULATIONS.

