Reveal | E24753-BKGLD

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Tubular pendants finished in Satin Nickel or Matte Black in contrasting Satin Brass or Gold bands respectively. Light shines downward from the bottom of the pendant as well as a reveal of light behind the band.



MEASUREMENTS

DIMENSION	: 11" L x 11" W x 12.25" H
MAX OAH	: 134" OAH
CANOPY	: 11" W x 1.75" H x 11" L
HANGING WEIGHT	: 5.94 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 1,440 Rated (350 Del.)
BULB	: 3 x 6W LED DC Integrated , 18W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Y
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black / Gold (BKGLD)

Satin Nickel / Satin Brass (SNSBR)

MATERIAL

Steel, Aluminum, Acrylic

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com