



Technical Data

Color	Black
Sizes Available	S-L
Polymer	Butyl
Thickness	13 Mil
Dip	Single
Length	11"
Grip	Smooth
Construction	Unsupported, Waterproof
Case Dimensions (in)	32.00 x 21.00 x 15.00
Case Weight (lbs)	60.01
Packed	288 Pair/Case
Packaging	Bulk Pack
Certifications	TAA Compliant
Country of Origin	United States

North® Butyl™

13 Mil Butyl Rubber Glove with Smooth Grip - 11" - Ink Free

- Ink free (IF) eliminates the risk of ink from the back of hand logo leaching or reacting with aggressive chemicals (like ketones, acids, or solvents)
- Exceptional resistance to a broad range of toxic chemicals: making it the only suitable for many critical applications
- Highly resistant to ketones (MEK: MIBK: acetone) and esters (tricresyl phosphate: amyl acetate: ethyl acetate)
- Solvent based: multi-dip manufacturing process provides multiple layers of polymer (like a glove within a glove) which results in a glove of superior quality
- Butyl provides the highest permeation resistance to vapors and gases

Performance Data

EN 374-5

Bacteria and Fungi

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
B131/7S/IF	Black	S	883940454306		
B131/8M/IF	Black	M	883940384078		00883940384085
B131/9L/IF	Black	L	883940384092		00883940384108
B131/10XL/IF	Black	XL	198987092030	10198987092037	20198987092034