



COVE™

Crystal Wall Sconce



SKU	Model #
157034	JXL-BD12-BG12W-5CCT

The COVE Crystal Glass Wall Sconce by Beyond LED Technology is an elegant and modern lighting solution designed to elevate the ambiance of any space. Its sophisticated design, featuring a bubble-textured crystal glass panel, creates a soft, diffused light that reduces glare while providing a warm, inviting glow. Perfect for both residential and commercial applications, this sleek fixture is ideal for enhancing the atmosphere of hotel lobbies, hallways, patios, and entryways. The combination of durable aluminum, metal, and crystal glass ensures a timeless aesthetic and long-lasting performance, making it a perfect choice for high-end commercial environments and luxury spaces.

Product Features

- 12 Watt
- Adjustable CCT
- 180° Beam Angle
- Aluminum, Metal, and Crystal Glass Construction
- Input Voltage 120VAC
- ETL listed
- 3-year warranty

COVE™

Crystal Wall Sconce



SKU	WATT	MAX LUMENS	ADJ. CCT	INPUT VOLTAGE	CRI	FIXTURE SIZE	LIGHT SPREAD	CONSTRUCTION	IP RATING	CERTIFICATIONS
157034	12W	420	2700K/3K/ 3500K/ 4K/5K	120V	>80	12.2"	180°	Aluminum + Metal + Glass	IP65	ETL

SKU: 157034

Specifications

Parameter	Description	Value
General Performance	Model #	JXL-BD12-BG12W-5CCT
	Watt	12W
	Max Lumens	420
	Lumen Efficacy	Up to 50LM/W
	Color Temperature	2700K / 3000K / 3500K / 4000K / 5000K
	CRI (Ra)	>80
	Light Spread	180°
	Diffuser Type	Glass
Electrical	Input Voltage	100-277Vac
	Frequency	50/60Hz
	Dimming	N/A
	Power Factor	≥0.95
	Driver Surge Protection	<1000V
	Flicker Percent	<30%
Physical	Operating Temperature	-20°C to 40°C
	Operating Humidity	10% ~ 40%RH
	Storage Temperature	-20°C to 60°C
	Storage Humidity	10%-90%RH
	LED Brand	San'an
	LED Type	SMD3030
	LED QTY	12 Pcs
	Construction	Aluminium + Metal + Glass
Qualification	Housing Color	Matte Black
	IP Rating	IP65
	Warranty	3 Years


CRYSTAL WALL SCONCE




COVE™

Crystal Wall Sconce

Correlated Color Temperature (CCT)



Dimensions



COVE™

Crystal Wall Sconce




Installation

FIXTURE INSTALLATION


Important: Read all instructions in order to ensure safety and proper installation.

DO NOT operate this product under any conditions other than those for which it is specified. Failure to observe these precautions can lead to electrical shock, product failure, or other problems.



PARTS LIST

- ① LED Chip
- ② LED Fixture
- ③ Wire
- ④ Mounting Plate
- ⑤ CCT Adjustable Switch



Specification	Wattage	Input Voltage	Dimensions L x W x H	Equivalent to
12' LED Crystal Bubble Glass Wall Light	12W	120Vac	5" x 12" x 3.66"	42W

MAINTENANCE

READ ALL INSTRUCTIONS IN ORDER TO ENSURE SAFETY AND PROPER INSTALLATION.

1. DO NOT operate this product under ANY conditions other than those specified for it. Failure to observe these precautions can lead to electrical shock, product failure or other problems.
2. TURN OFF THE POWER at the electrical panel before installation or maintenance.
3. DO NOT modify this fixture. ANY modifications may render the product unsafe and void the warranty.
4. This product is rated for outdoor use.



COVE™

Crystal Wall Sconce

Installation

Limited Warranty

The warranty applies to the product from the original date of purchase for three (3) years against manufacturing defects. The owner must provide a copy of the original proof of purchase. The manufacturer's obligation under this warranty is limited to repairing or replacing the component. It is not related in any way to the cost of the connection, the installation of the replacement parts or cost of transport.

Package Content


- Wall Lamp x 1
- Wire Connectors x 3
- Screws x 4
- Mounting plate x 1



WARNING

Turn power OFF from electrical panel before installation or maintenance.

1. Take off the mounting bracket from the light fixture.
2. Attached the mounting bracket to the J-box /wall by 2 screws.
3. Use wire connectors to make all wire connections. Twist connectors until wires are tightly joined together
4. Select your ideal CCT through the CCT switch.
5. Fix the light fixture to the mounting bracket by 2 screws on the side.
6. Using exterior grade caulk, caulk the gap between the luminaire and mounting surface, do not caulk the bottom of the fixture backplate to ensure proper moisture drainage. Installation is done.



COVE™

Crystal Wall Sconce



Packaging

SKU	Box Dimension	Qty	Net Weight	Gross Weight
157034	17.08" x 15.66" x 14.96"	6 Pcs/Box		

Application Picture



CRYSTAL WALL SCONCE

Warranty

This product is covered under a 3-year warranty. For complete warranty details, [Click Here.](#)