

# 0-10V Dual Tech Occupancy Sensor Dimmer

Greengate

- 3-in-1 solution that combines functionality of a switchpack, a sensor and a 0-10V dimmer
- Saves labor costs, reduces installation time and meets energy codes and standards
- Ultrasonic occupancy (US) and passive infrared (PIR) sensing; Daylight harvesting
- Can be used in single-pole (1 location) as well as 3-way (multi-location) applications
- Compatible with Cooper Lighting Solutions' decorator style devices and wallplates



OSW-D-010-W



Catalog Number	Product Description	Finish	Voltage	Watts	Detection Type	Coverage	Pallet Quantity	UPC
OSW-D-010-W	0-10V Dimmer, OCC Sensor	White	120/277V	960W/2200W	PIR and Ultrasonic	1000 sq. ft.	1,200	080083816071

# NeoSwitch ONW Occupancy Wall Sensor

Greengate

- Passive Infrared (PIR) single level occupancy sensing switch for motion sensing control
- Also a conventional wall switch; Designed for energy savings and convenience
- Detects motion from a heat-emitting source (such as a person entering a room) within its field-of-view and automatically switches lights ON
- Neutral and non-neutral wiring options for installation; Ideal for retrofit applications



ONW-P-1001-DMV-W

ONW-D-1001-DMV-W



Catalog Number	Product Description	Finish	Voltage	Watts	Detection Type	Coverage	Pallet Quantity	UPC
ONW-P-1001-MV-W	PIR Wall Sensor	White	120/277V	1200W/2200W	PIR	1000 sq. ft.	900	080083523863
ONW-D-1001-MV-W	Dual Tech Wall Sensor	White	120/277V	1200W/2200W	PIR and Ultrasonic	1000 sq. ft.	900	080083524709
ONW-D-1001-MV-N-W	Dual Tech Wall Sensor, Neutral required	White	120/277V	1200W/2200W	PIR and Ultrasonic	1000 sq. ft.	900	080083524594

# OAC MicroSet Dual Tech Ceiling Sensors

Greengate

- Combines ultrasonic and Passive Infrared (PIR) technologies, eliminates false deactivations
- MicroSet self-adjusting technology provides an adaptive and airflow tolerant technology
- Ideal for spaces that have increased airflow due to higher occupant levels
- Drastically simplifies and reduces installation and adjustment time
- Available in line-voltage and low-voltage versions; Compatible with SP20 switchpacks



Catalog Number	Product Description	Finish	Voltage	Watts	Detection Type	Coverage	Pallet Quantity	UPC
OAC-DT-2000-MV	DT Ceiling Mount, Line Voltage	White	120-347V	1200W-2700W	PIR and Ultrasonic	2000 sq. ft.	450	080083579426
OAC-DT-2000	DT Ceiling Mount, Low Voltage	White	10-30VDC	N/A	PIR and Ultrasonic	2000 sq. ft.	450	080083579266
OAC-DT-2000-R	DT Ceiling Mount, Isolated Relay	White	10-30VDC	N/A	PIR and Ultrasonic	2000 sq. ft.	450	080083702077
OAC-DT-1000	DT Ceiling Mount, Low Voltage	White	10-30VDC	N/A	PIR and Ultrasonic	1000 sq. ft.	540	080083579242
OAC-DT-1000-R	DT Ceiling Mount, Isolated Relay	White	10-30VDC	N/A	PIR and Ultrasonic	1000 sq. ft.	540	080083702060
OAC-DT-0501	DT Ceiling Mount, Low Voltage	White	10-30VDC	N/A	PIR and Ultrasonic	500 sq. ft.	450	080083579228
OAC-P-1500-R	Low Voltage Ceiling Sensor	White	10-30VDC	N/A	N/A	N/A	800	080083579150