



## Protect It! 8-Outlet Surge Protector, 10 ft. (3.05 m) Cord, 3240 Joules, Tel/Fax/Modem/Coax Protection, RJ11

MODEL NUMBER: TLP810SAT



### Highlights

- 8 outlets / 10-ft. (3.05 m) cord
- 3240 joule rating
- 2 sets of 2.2GHz gold coaxial/satellite surge protection jacks bandwidths)
- Modem/fax surge protection

### Package Includes

- TLP810SAT Surge Suppressor
- 6-ft. (1.83 m) telephone cable
- Two 6-ft. (1.83 m) coax cables
- Instruction manual with warranty information

### Description

Tripp Lite's TLP810SAT Surge Suppressor offers complete AC, telephone and coax line surge suppression on two lines for comprehensive system protection of home theaters, A/V systems and desktop PCs. Heavy grade AC surge suppression shields connected equipment from damage and performance problems due to the heaviest transient surges. Two sets of 2.2GHz gold coax connectors for cable-TV, satellite, broadcast antenna or cable modems. Set of RJ11 jacks offers surge suppression for pay-per-view satellite systems, dial-up and DSL modems, fax machines and cordless phones.

TLP810SAT offers 8 total outlets, 10-ft. (3.05 m) cord with space-saving angled plug and diagnostic LEDs with audible alarm to warn of wiring problems and suppressor damage. Network grade AC suppression rated at 3240 joules shields equipment from surges and line noise. Integrated child-safety outlet covers safely seal off unused outlets. Attractive black suppressor housing with keyhole mounting tabs and 3 designated transformer plug outlets offers convenient protection of entire home theatre, a/v and computer equipment and accessories. \$250,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

PLUG/OUTLETS: Input: NEMA5-15P/Output: 8 NEMA5-15R/10-ft. (3.05 m) AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet strip with transformer-spaced outlets

SUPPRESSION: AC: 150V RMS Clamping/3570 joules

PHONE: Set of phone jacks (RJ11, 2-wire, 1 line)

COAX: 2 Sets 2.2GHz gold coax jacks

### Features

- 3240 joules AC surge suppression shields equipment from the strongest surges and line noise
- 8 AC outlets with room for 3 transformer plugs without blocking outlets covers computers and all peripherals
- Phone line surge suppression protects both dialup and DSL modems, plus fax machines, cordless



phones and more (pair of RJ11 jacks, 2-wire, 1 line, includes 6-ft. (1.83 m) phone cable)

- Two sets of coax jacks protect cable modems, plus satellite, cable TV and broadcast antennas (includes 6-ft. (1.83 m) coax cable)
- Long 10-ft. (3.05 m) AC line cable with space-saving angle input plug conveniently reaches distant outlets
- Lighted power switch with integrated 15A circuit breaker offers power control and overload protection
- Integrated child-safety sliding outlet covers safely seal off all unused outlets
- Diagnostic LEDs confirm outlet grounding and surge suppression status
- Audible alarm offers notification of suppressor damage
- Attractive black suppressor housing with keyhole mounting tabs allow versatile placement options
- \$250,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

## Specifications

OVERVIEW	
UPC Code	037332095305
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	216000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Right-Angle Plug	Yes
Input Cord Length (m)	3.05
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(8) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(6) Yes



Outlet Orientation	Single row of 5, plus a second row of 3 for transformer accommodation
Right-Angle Outlets	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2-position red illuminated on/off power switch
Audible Alarm	Audible alarm sounds to indicate damage to suppression components
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	3240
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	330/400/400
EMI / RFI Filtering	Up to 40 dB
Automatic Shut-Off	Yes
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	2 line (2.2 GHz Bandwidth)
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	
Color	Black
Antimicrobial Coating	No
Color (AC Line Cord)	Black
Housing Color	Black
Integrated Keyhole Mounting Slots	Yes
Keyhole Slot Mounting Measurement (Center to Center)	Distance between horizontal tabs = 75mm; Distance between vertical tabs = 41.6mm
Material of Construction	Plastic
Outlets Measurement (Center to Center)	Distance between standard outlets = 28.5mm; Distance between transformer outlets = 57mm
Receptacle Color	Black
Shipping Dimensions (hwd / cm)	64.01 x 26.67 x 22.35



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Shipping Dimensions (hwd / in.)	25.20 x 10.50 x 8.80
Shipping Weight (kg)	1.32
Shipping Weight (lbs.)	2.90
Unit Dimensions (hwd / cm)	12.34 x 24.3 x 3.83
Unit Dimensions (hwd / in.)	4.86 x 9.55 x 1.51
Unit Weight (kg)	0.92
Unit Weight (lbs.)	2.02
<b>SPECIAL FEATURES</b>	
Rotatable Outlets	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Canada	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Revision
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
Industry Canada (Communications)	Industry Canada
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 <a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a>

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>