

ELIAS

F3628-FOR

The Elias chandelier brings organic texture to a bold architectural frame. A large woven Saguran drum shade lends warmth, while slender Forged Iron arms introduce graphic clarity. The light source is housed within a simple bowl, replacing a traditional candle cluster with a clean, modern silhouette. Available with 4 or 6 lights, it makes an approachable, yet substantive impression.

*Due to the one-of-a-kind nature of the medium, exact colors and patterns may vary slightly from the image shown.

FINISHES

FORGED IRON

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 25"

Width/Diameter: 28"

Minimum Height: 32.25"

Maximum Height: 102"

Canopy/Backplate: 5"

Hanging Type: 72" Chain

Product Weight: 14.3lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Natural Woven

Shade 1 Finish: Saguran

Shade 1 Top Width: 28"

Shade 1 Bottom L/W: 0" / 28"

Shade 1 Height: 12"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: B11

Max Wattage: 10

Bulb Quantity: 4

Wire Length: 144"

Cord Type: SPT-1 SILVER W/ TINNED GROUND
WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 33" x 33" x 30"

Carton 1 Weight: 31lb

Shipping Method: Truck Only

Country of Origin: PH

