



Southwire™

TOOLS & EQUIPMENT

Wobblelight® Jr. LED



The 27" tall, patented self-righting Wobblelight® Jr. LED is a work light that can withstand rough use, on and off the jobsite. This 9000 lumen LED light runs cool and is ideal for providing temporary lighting in areas up to 35 feet in diameter. Bright, portable, and durable, the Wobblelight® Jr. LED will reliably deliver lighting when you need it most.

9,000
Lumens

360°
Lighting

Integrated
Handle

No Hot
Surfaces

5' Integrated
Power Cord with
NEMA 5-15 Plug

Silicon Ring
for Lamp
Stability

LED bulb
included

Patented
Self-Righting
Technology

Model No.	Lumens	Lighting Range	Bulb Type	Lamp Life (hrs)	Kelvins	Watts	Amp Draw	Voltage	Temp Rated	Tested	Cord Type	Weight
111206	9,000	35 ft.	LED	35,000	5,000	80	.7	120V	-40°F - 125°F	cUL	18/2 SJTW	13.9 lbs

BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™

1-855-798-6657 | [SOUTHWIRETOOLS.COM](https://www.southwiretools.com)

©2019 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.