


PRODUCT DESCRIPTION



MEASUREMENTS

DIMENSION	: 5" L x 5" W x 8.25" H
CANOPY	: 5" W x 1" H x 5" L
HANGING WEIGHT	: 1.68 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 600 Rated (590 Del.)
BULB	: 1 x 6W LED PCB Integrated , 6W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: TriacÂ orÂ ELVÂ atÂ 120V
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Down

FINISHES OPTION

- Black (BK)
- Brushed Aluminum (AL)
- Natural Aged Brass (NAB)
- White (WT)

MATERIAL

Alumimum, Steel, PC

RATINGS

cETLus
Dry Location
Energy Star
CA Title 24

ADDITIONAL

INSTALL UP/DOWN: Down
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com