

OSSIAN

B6428-BRZ

An industrial-modern sconce with graphic appeal, Ossian combines smooth curves and an allover Bronze materiality to create an edgy exterior staple. Its tubular shape creates a unique C-shaped channel that is intersected by a wide belt at the center, concealing the light source. As the channel fills with light, this graphic sconce casts an ambient glow around an outside area.

FINISHES

BRONZE

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 28"

Width/Diameter: 4.75"

Canopy/Backplate: 4.75"

Product Weight: 3.87lb

Extension: 5.25"

Top to Center: 14"

Canopy/Backplate Shape: Rectangle

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: Yes

Shade

Shade 1: Acrylic

Shade 1 Finish: Clear Inside Etched

Shade 1 Top Width: 2.75"

Shade 1 Height: 0.75"

ELECTRICAL



Bulb 1

Bulb Included: N/A

Socket: Integrated LED

Max Wattage: 17

Bulb Quantity: 1

Bulb Included: No

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Dimmer Type: ELV, TRIAC

Gem Box Required (2"x3"): No

Dark Sky: No

CRI: 90

Color Temp.: 3000k

Lumens: 150

Title 24: No

Field Serviceable: No

SHIPPING

Carton 1: 32" x 8" x 8"

Carton 1 Weight: 6lb

Shipping Method: Ground

Country of Origin: CN

