



PIP® Stromboli™

Cap Style Smooth Dome Hard Hat with Heat Resistant ABS/Polycarbonate Shell, 4-Point Textile Suspension and Wheel-Ratchet Adjustment

- Lightweight shell made with UV stabilized ABS/Polycarbonate shell reduces worker fatigue
- Smooth dome styling is popular in construction, welding and metal working
- Meets -ANSI/ISEA Z89.1 Type I and CSA Z94.1 Type I requirements
- Fulfills Class E Electrical Insulation requirements
- 4-Point quick release suspension with strong textile straps and crown comfort pad provides a comfortable and secure fit
- Non-chaffing, replaceable foam sweatband for maximum sweat absorption

Applications

- Mining
- Tunneling
- Demolition
- Utility Work
- Metalworking

Technical Data

Color	Forest Green, Steel Blue, Dark Green, Lime, Orange, Yellow, Black, White, Red, Gray
Sizes Available	OS
Packaging	Bagged Each
Packed	12/Case
Case Dimensions (in)	20.30 x 14.00 x 28.10
Case Weight (lbs)	11.46
Country of Origin	Canada
Shell Material	ABS / Polycarbonate
Shell	Non-Vented
Brim Style	Cap Style
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Suspension	4 Point Nylon Webbing Cradle
Sweatband	Felt Lined Foam
Size Range	53cm-63cm
Certifications	ANSI/ISEA Z89.1, CSA Z94.1 Certified, TAA Compliant

Performance Data

ANSI Type	Type I
Electrical Class	Class E

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-HP841R-11	Black	OS	620606002941	10616314299374	10620606002948
280-HP841R-04	Dark Green	OS	620606003702	10616314299411	10620606003709
280-HP841R-74	Forest Green	OS	620606002972	10616314299459	10620606002979
280-HP841R-09	Gray	OS	620606002934	10616314299459	10620606002931
280-HP841R-45	Lime	OS	620606003504	10616314299534	10620606003501
280-HP841R-03	Orange	OS	620606002927	10616314299534	10620606002924
280-HP841R-15	Red	OS	620606002958	10616314299619	10620606002955
280-HP841R-71	Steel Blue	OS	620606002965	10616314299657	10620606002962
280-HP841R-01	White	OS	620606002903	10616314299695	10620606002900
280-HP841R-02	Yellow	OS	620606002910	10616314299695	10620606002917