

**Garant****Micro-boring head Digital Ø 0.3 - 7.1 mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 237493        |
| GTIN         | 4045197816436 |
| Item class   | 29W           |

**Description****Version:**

**Adjustment accuracy 0.01 mm per graduation / with vernier 0.002 mm on the Ø.**

**Digital** boring heads with **additional precise reading facility** on **0.001 mm in Ø** via **digital display unit No. 237601** (order separately).

Ø adjustment with minimum backlash thanks to direct measuring system.

**Application:**

With cutting insert No. 237621, adapter No. 237624 and insert No. 237625.

**Technical description**

|                           |             |
|---------------------------|-------------|
| External Ø D <sub>1</sub> | 25 mm       |
| Ø D <sub>3</sub>          | 4 mm        |
| Reach L <sub>1</sub>      | 25 mm       |
| Shank Ø D <sub>2</sub>    | 10 mm       |
| Through-coolant           | yes         |
| Type of product           | Boring tool |

