



Fibre-Metal® Roughneck™ P2

Type I, Non-Vented, Cap-Style Smooth Dome Hard Hat with Heat Resistant Fiberglass Shell, 8-Point SuperEight™ Suspension and Wheel Ratchet Adjustment, Includes Quick-Lok® Accessory

- Fiberglass-resin compound
- Chip and nick resistant
- Molded-in color
- Smooth matte finish
- Heat resistant up to 370°F (188°C)
- Eight-point suspension

Technical Data

Color	Blue, Green, Orange, Red, White, Black, Yellow, Gray
Sizes Available	OS
Packaging	Bagged Each
Packed	20/Case
Case Dimensions (in)	23.00 x 19.00 x 23.00
Case Weight (lbs)	22.99
Country of Origin	Mexico
Shell Material	Fiberglass Composite
Shell	Non-Vented
Brim Style	Cap Style
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Certifications	ANSI/ISEA Z89.1, CSA Z94.1 Certified, TAA Compliant

Performance Data

ANSI Type	Type I
Electrical Class	Class G

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
P2AQRW11A000	Black	OS	883940087887		00883940087894
P2AQRW71A000	Blue	OS	883940088723		00883940088730
P2AQRW09A000	Gray	OS	883940087863		00883940087870
P2AQRW74A000	Green	OS	883940088747		00883940088754
P2AQRW46A000	Orange	OS	883940087948		00883940087955
P2AQRW15A000	Red	OS	883940087924		00883940087931
P2AQRW01A000	White	OS	883940088686		00883940088693
P2AQRW02A000	Yellow	OS	883940088709		00883940088716