Marsh | E24099-BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Drawing the outdoors in, the inspiration for this piece combines iconic modern lighting with biophilic forms. Long slender armatures descend in organic slopes to domed, ovoid shades that appear leaf-like. Finished in Matte Black the collection features coordinating low voltage garden lights that blend into outdoor spaces while providing useful illumination.



MEASUREMENTS

DIMENSION	: 25" L x 25" W x 41" H
MAX OAH	: 7.75" W x 7.75" H
HANGING WEIGHT	: 6.16 lb

LAMPING

INPUT VOLTAGE	: 12V
LUMENS	: 1,500 Rated (900 Del.)
BULB	: 3 x 5W LED AC Integrated , 15W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Y
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)

MATERIAL

Aluminum

RATINGS

cETLus
Wet Location

ADDITIONAL

RATED LIFE 25000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com