13 In. 15W Selectable Color LED Light Fixture

Features

- Ultra-modern slim edge-lit design makes any room architecturally pleasing
- Preset color temperature or adjust after install. Get warm, cool or daylight with a flip of a switch
- Flexible installation as either ceiling flush mount or a wall sconce
- **Ideal usage:** Recessed Lighting
- **Special Features:** Color Selectable



Specifications

Item Number	Item Length (In)	Item Width (In)	Item Height (In)
FP13/4WY/NK	13.1	13.1	1.1
Fixture Type	**Fixture Finish**	**Fixture Lens Material**	**Fixture Mount**
Edge-Lit Flat Panel	Aluminum	Plastic	Recessed
Fixture Color	**Technology**	**Brightness (LUMENS)**	**Lumen Efficiency (LPW)**
Nickel	LED - SMD	1050	70.0
Color Accuracy (CRI)	**Color Temperature (CCT)**	**Life Hours**	**Life Years**
80	3000|4000|5000	50000	45.7
Voltage (V)	**Annual Energy Cost ($)**	**Energy Used (Wattage)**	**Battery Operated**
120	1.81	15	No
Pack Quantity	**Bulbs Included**	**Smart**	**Portable**
1	Yes	No	No
Dimmable	**Hardwire**	**Enclosed Fixture Rated**	**Safety Location**
Yes	Yes	No	Damp
CEC Compliant	**Warranty Years**		
Not Regulated	5		