SATCO | NUVO



Project / Job Name:

Location:

Fixture Type:

Notes:

**S30113** - LED Collapsible Lantern; 1200 Max Lumens; USB-C Rechargeable; 3.7 Volt; 6pc Tray Pack

DIMMABLE FC RoHS COMPLIANT 1 YEAR WARRANTY

## GENERAL

| | |
|---|---|
| Company | SATCO |
| EA Height | 5.0 |
| EA Width | 5.0 |
| EA Length | 2.25 |
| Material | ABS Plastic / Silicone / Polycarbonate (PC) |
| Fixture Type | Rechargeable Lantern |
| Includes | USB-A to USB-C Charging Cable |
| Product Notes | Integrated Rechargeable 3.7V Li-ion Battery; Power Bank: 2000mAh; Charge Time: 3.5HRS |
| Status | Active |
| CCT Selectable | No |
| Wattage Selectable | No |
| Finish Family | Black |
| Additional Info | Ships in retail-ready display trays and packaging |
| Integrated Features | Power Bank; Bottom Carry Handle; Expandable; Collapsible; Strobe |
| Lens Finish | Clear |
| Lens Material | Silicone |
| Lensed | Yes |
| Portable Light Modes | Emergency Strobe, High, Low, Medium |
| Product Technology | LED |
| Serviceable Battery | No |
| Beam Distance (Ft) | 66 |
| Battery Indicator | No |
| Digital Display | No |
| Drop Impact Rating | 3.28 Ft (1M) |
| Battery Operating Temp | +32F to +104F (0C to +40C) |
| Light Source Quantity | Single |
| Power Bank Storage | 2000mAh |

## ELECTRICAL

| | |
|---|---|
| CCT (Kelvin Temp) | 4500K |
| Dimmable | Yes-Dimmable |
| Beam Angle (degree) | 360 |
| Color Temp | Cool White |
| CRI | 50+ |
| Dimming Type | Only dimmable via setting selection, Step Dimming |
| Operating Temp | +32F to +104F (0C to +40C) |
| Lumens | 1200L/600L/140L |
| Volts | 3.7V |
| Max Lumens | 1200L |
| Connection | USB-C Rechargeable |
| Charge Time | 3.5hr |
| Battery Chemistry | Lithium-ion (Li-ion) |
| Replaceable Battery Type | 18650 |
| USB Type In | 1 USB-C |
| USB Output Charging Power | (1) 1A 5V |
| USB Type Out | 1 USB-A 1A |

## PHYSICAL

| | |
|---|---|
| Finish | Black / Gray / Red |
| Housing Color | BlackGrayRed |
| Mounting Procedure | Hang Hook |

## ADDITIONAL INFO

| | |
|---|---|
| Warranty | 1-Year |
| Installation Notes | Do Not Charge The Product Below 40F Or above 104F; Do Not Exceed 5V DC, 1A Charging |
| Portable Light Functions | Red Light Function, White Light Function |

## PACKAGING

| | |
|---|---|
| UPC | 045923300141 |
| Case Cube | 0.7704 |
| Case Height | 7.28 |
| Case Length | 11.61 |
| Case Quantity | 12 |
| Case UPC | 10045923300148 |
| Case Weight | 9.92 |
| Case Width | 15.75 |
| EA Cube | 0.0326 |
| EA Height | 5.0 |
| EA Length | 2.25 |
| EA Quantity | 1 |
| EA Weight | 0.66 |
| EA Width | 5.0 |
| Inner Cube | 0.2563 |
| Inner Height | 6.1 |
| Inner Length | 7.09 |
| Inner Quantity | 6 |
| Inner UPC | 20045923300145 |
| Inner Weight | 4.63 |
| Inner Width | 10.24 |
| Pack Type | Color Box |
| Web Height | 5.1 |
| Web Length | 4.69 |
| Web Width | 4.69 |

## COMPLIANCE

| | |
|---|---|
| CA Prop 65 | Lead |
| FCC Compliant | Yes |
| ROHS Compliant | Yes |
| Energy Star Certified | No |
| T24/JA8 Compliant | No |
| Performance Standards | ANSI PLATO FL1 |



© Satco Products, Inc.
All rights reserved 2026