

KENSINGTON

MDS2102-AGB

FINISHES

AGED BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 19"

Width/Diameter: 14.75"

Minimum Height: 24.25"

Maximum Height: 76"

Canopy/Backplate: 4.75"

Hanging Type: 54" Chain

Product Weight: 4.334lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: Yes

Living Finish: Yes

Uplight Only: No

Shade

Shade 1: Walnut Rattan

Shade 1 Top Width: 2.25"

Shade 1 Bottom L/W: 14.75" / 0"

Shade 1 Height: 16"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: A21

Max Wattage: 25

Bulb Quantity: 1

Bulb Included: No

Wire Length: 120"

Cord Type: SPT-1 SILVER W/ TINNED GROUND
WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 19" x 19" x 26"

Carton 1 Weight: 9lb

Shipping Method: Ground

Country of Origin: VN

