



PIP® V2™

V2 Cap Mounted Passive Ear Muff - NRR 24

- Length is easily adjustable to achieve a perfect fit
- Extra soft memory foam ear cushions conform to surface and head shape to ensure optimum wearer comfort
- 360° rotation for standby and resting positions
- Universal adaptor with slot for visor carrier
- Bright Color coding with v1™, v2™, v3™ noise protection indicator for easy selection and identification
- Replacement hygiene kits available separately

Technical Data

Color	Neon Orange
Sizes Available	OS
Packaging	Boxed
Packed	20 Pair/Case
Case Dimensions (in)	24.41 x 13.39 x 14.96
Case Weight (lbs)	14.99
Country of Origin	China
Hearing Style	Cap Mounted
Protection Type	Passive
Product Circularity	Reusable / Launderable

Performance Data

NRR Rating (ANSI S3.19-1974)	24
SLC 80 Class	Class

Care Instructions

Routinely wash with mild soap and water. Allow cushions to air dry.

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-16

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
263-V2CM	Neon Orange	OS	616314722820	10616314722827	20616314722824