



jalas® SPOC 5462

ASTM F2892-18 SD 35 ASTM F3445-21 SR EN ISO 20347:2012 01, SRC, FO, A, E

Learn more

FOR THE HEALTHCARE SECTOR, WITH BOA®

A comfortable and certified lightweight shoe with high breathability for use in healthcare work environments. The shoe is tested and approved for slip-resistance and has shock-absorbing soles in multiple layers for personal protection. Textile mesh fabric with high breathability makes the shoe cool, the BOA® Fit System on the side gives a perfect fit and the sock-like construction increases comfort. ESD certified for protection of sensitive electronic equipment. All models are unisex.

CHARACTERISTICS

- Excellent grip
- Perfect fit
- Extra comfortable
- Breathable
- Excellent shock absorption
- Light

FUNCTIONS

- Breathable mesh
- Low weight
- Anti-static properties
- BOA® Fit System
- Double shock absorption zones
- Conforms with IEC 61340-5-1 (ESD)

BOA DIALED IN. PRECISION FIT.

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Prevents risk of: , Sprain injuries, Antistatic, Slipping, Strain injuries

PRIMARY ENVIRONMENTS OF USE

Outdoors, Indoors, Office environments, Slippery environments

PRIMARY AREAS OF USE

Care work, Healthcare, Office work

SPECIFICATION

TYPE Occupational footwear, Low shoes
CATEGORY Cat. II
FITTING Regular
COLLECTION SpOc
UPPER MATERIAL Textile
LINING MATERIAL Polyester
INSOLE JALAS FX2 Pro SpOc
INNERSOLE MATERIAL Textile, Soft EVA, Polyester-based conductive thread, Double shock absorption zones in PORON® XRD®
MIDSOLE MATERIAL EVA
OUTSOLE MATERIAL Nitrile rubber outsole
FASTENING BOA® Fit System
COLOUR White
NET WEIGHT, (SIZE 42) 0.73 kg

COMPLIANCE

CE Cat. II

EAC TP TC 017:2011

ASTM F2892-18
SD 35

ASTM F3445-21
SR

EN ISO 20347:2012
01, SRC, FO, A, E

FEATURES

Anti-static properties

Ergothan Shock Absorption System

ESD

Oil-resistant outsole

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
35	2	3.5	4	5462-35	6408487532511
36	3	4	5	5462-36	6408487532559
37	4	5	6	5462-37	6408487532597
38	5	5.5	6.5	5462-38	6408487532634
39	6	6.5	7.5	5462-39	6408487532672
40	6.5	7.5	8.5	5462-40	6408487532719
41	7	8	9	5462-41	6408487532757
42	8	9	10	5462-42	6408487532795
43	9	9.5	11	5462-43	6408487532832
44	10	10.5	11.5	5462-44	6408487532870
45	10.5	11	12.5	5462-45	6408487532917
46	11	12	13	5462-46	6408487532955
47	12	13	14	5462-47	6408487532993
48	13	13.5	14.5	5462-48	6408487533037

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.